


т	۵	п –	m	0	
					_







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 17

PLATING : M = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ω

-Standard : Based on MIL-DTL-38999 Series III

	-Shell Material	: Composite
	-Shell Plating	: Nickel
	-Insulator	: Thermoplastic
	-Contacts	: Copper Alloy
	-Seals & Grommet	: Silicon Elastomer
N	-Contact Plating	: Gold over copper Alloy 0.8µm minimum
	-Durability	: 500 Mating cycles
	-Delivered without Sou	uriau contacts
	-Temperature Range	: -65°C to +200°C
	-Salt Spray	: 2000 hours
	-Mass	: 23.2 g ± 10%

8D 0

G

17

Μ

06

S

F

N L

Dim	Nominal
Р	3.25±0.2
PP	4.93±0.2
R1	26.97
R2	24.61
S	33.3±0.3
V'	19.5+1.4/-0
W'	2.1/3.65
Z'	32 Max
VV THREAD	M25x1-6g


Delivered W/O Contacts


CONTACT LAYOUT : 17-06

CONTACT TYPE : SOCKET(500 Matings)

Е

ORIENTATION : N





œ		А				
			4			
S EXAMPLE			3			
any non-conformity or damage which does not comply with er of the Parties or by a third party idation, technical notice.)						
	CUSTOMER DE	MOD N°				
ite Receptacle 8D series						
ar	NPRDS / PR 859	OJECT	1			
I.COM	communicated without permission					
U DRG N° M06SNL-C		SHEET				
B		A				

