


			-	
	m	п п	G	工







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 17

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Composite
-Shell Plating	: Olive drab Cadmium
-Insulator	: Thermoplastic
-Contacts	: Copper Alloy
-Seals & Grommet	: Silicon Elastomer
-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum
-Durability	: 500 Mating cycles
-Delivered with Souriau	contacts and Accessories
-Temperature Range	-65℃ to +175℃
-Salt Spray	: 2000 hours
	-Shell Plating -Insulator -Contacts -Seals & Grommet -Contact Plating -Durability -Delivered with Souriau -Temperature Range

: 22.8 g ± 10%

8D 0

G

17

J

26

А

F

В


Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
PP	4.93±0.2			
R1	26.97			
R2	24.61			
S	33.3±0.3			
V	19.5+1.4/-0			
W'	2.1/3.65			
Ζ'	32 Max			
VV THREAD	M25x1-6g			


ORIENTATION : B

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 17-26





	σ		A				
		I					
					4		
SEXA	MPLE				3		
whic er of tl idatio	non-conformit h does not co he Parties or k n, technical n	mply with by a third part otice.)					
Intry R	Jurisd	liction & Cont Not Listed	rol List		2		
.7J2	26AB						
				MOD N°			
ite l	customer drawing e Receptacle 8D series						
ar	NPRDS / PROJECT						
			59		1		
l.CC	COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
	DRG N°			SHEET			
'J26	SAB-C			1/2	J		
	В		А				

