

CLOCK OSCILLATOR

Page 1 of 3

CO1100-25.000

ELECTRICAL SPECIFICATION

PARAMETER	SYMBOL	CONDITIONS	VALUE	UNIT
Nominal Frequency	fo	Ta=25°C	25.000	MHz
Supply voltage, nom.	Vcc	Vcc ±10%	5	V
Supply current, max.	ls	Vcc=5.0 VDC; Ta=+25°C; Load=15 pF CMOS	50	mA
Operating Temperature Range	Ta	-	-0 to +70	°C
Storage Temperature Range	T(stg)	-	-55 ~ 125	°C
Frequency Stability	Δf/fo	Inclusive of 25°C Tolerance and Changes due to Operating Temperature, Supply Voltage, Load, Aging, Shock and Vibration	±100	ppm
Output Voltage Levels	V_{OL}	Logic "0" Level,	10% x Vcc	VDC
Output Voltage Levels	Voн	Logic "1" Level	90% x Vcc	VDC
Output Load		1 to 10 TTL Output		
Symmetry (Duty cycle)	DC	@ 50% of signal (Vdd)	4060	%
Rise time / Fall time, max.	tr / tf	tf 20%~80% Vout, 80%~20% Vout, 10		ns

MECHANICAL SPECIFICATION






Photo is not actual part


PIN CONNECTION			
PIN	FUNCTION		
1	nc		
7	Ground		
8	Output		
14	Vcc		





CO1100-25.000

REFLOW PROFILE



Reflow profile			
Temperature Min Preheat	T _{SMIN}	150°C	
Temperature Max Preheat	T _{SMAX}	200°C	
Time (T _{SMIN} to T _{SMAX})	ts	60-180 sec.	
Temperature	TL	217°C	
Peak Temperature	T _P	260°C max.	
Ramp-up rate	Rup	3°C/sec max.	
Ramp-down rate	R _{DOWN}	6°C/sec max.	
Time within 5°C of Peak Temperature	t _P	10 sec.	
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.	
Time	t∟	60-150 sec.	

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH-SVHC	Compliant
HALOGEN-FREE	Compliant
TERMINATION FINISH	Sn





CLOCK OSCILLATOR

Page 3 of 3

CO1100-25.000

MARKING

CO1100 25.000 •Rxxyyww

x – Internal Production ID code

y - Year code

w - Week code

YEAR CODE			
Year	Code		
2011	1		
2012	2		
2013	3		
2014	4		
2015	5		
2016	6		
2017	7		
2018	8		
2019	9		

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	a	19	S	37	K
2	b	20	t	38	L
3	c	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	0
6	f	24	Х	42	P
7	g	25	у	43	Q
8	h	26	Z	44	R
9	i	27	A	45	S
10	j	28	В	46	T
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	Е	49	W
14	n	32	F	50	X
15	О	33	G	51	Y
16	p	34	Н	52	Z
17	q	35	I		
18	r	36	J		

APPROVAL

RALTRON		
DRAWN BY:	AR, May 26, 2020	
APPROVED BY:	CP, May 26, 2020	
REVISION:	A, Initial Release	

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not sasume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.