_				
<b>—</b>	ם ا	н т -	п	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

ယ

 $\sim$ 

-Mass

BASIC SERIES:

SHELL SIZE : 17

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

2	-Shell Material	: Composite		
	-Shell Plating	: Olive drab Cadmium		
	-Insulator	: Thermoplastic		
	-Contacts	: Copper Alloy		
	-Seals & Grommet	: Silicon Elastomer		
	-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum		
	-Durability	: 500 Mating cycles		
	-Delivered with Souriau contacts and Accessories			
	-Temperature Range	: −65°C to +175°C		
	-Salt Spray	: 2000 hours		

: 33.6 g ± 10%

8D 0

G

17

J

26

В

F

В

Connector dimension					
Dim	Nominal				
Р	3.25±0.2				
PP	4.93±0.2				
R1	26.97				
R2	24.61				
S	33.3±0.3				
V	19.5+1.4/-0				
W'	2.1/3.65				
Ζ'	32 Max				
VV THREAD	M25x1-6g				


**ORIENTATION : B** 

CONTACT LAYOUT : 17-26

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for a due to a use of the Products the Specifications issued by either (professional recommend



	σ		A				
AS EXA	AMPLE				3		
s whic er of t	ny non-conformity or damage vhich does not comply with of the Parties or by a third party ation, technical notice.)						
untry FR	/ Jurisdiction & Control List Not Listed						
.7J2	J26BB						
				MOD N°			
		CUSTOMER	R DRAWING				
site	e Receptacle 8D series						
ar :			PROJECT <b>59</b>		1		
	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
	U DRG N°						
'J2(	6BB-C		A	1/2	J		

