




### **Features:**

- 24 dBm of Power at 18 GHz
- 14 dB Small Signal Gain at 18 GHz
- 45% typical PAE at 18 GHz
- 0.25 x 300 Micron Refractory Metal/Gold Gate
- Excellent for Medium Power, Gain, and High Power Added Efficiency
- Ideal for Commercial, Military, Hi-Rel Space Applications



Chip Dimensions: 415 x 315 microns Chip Thickness: 100 microns

## **Description:**

The MwT-PH33F is a AlGaAs/InGaAs pHEMT (Pseudomorphic-High-Electron-Mobility-Transistor) device whose nominal 0.25 micron gate length and 300 micron gate width make it ideally suited for applications requiring high-gain and medium power up to 26 GHz frequency range. The device is equally effective for either wideband (e.g. 6 to 18 GHz) or narrow-band applications. The chip is produced using reliable metal systems and passivated to insure excellent reliability.

## Electrical Specifications: at Ta= 25 °C

PARAMETERS & CONDITIONS	SYMBOL	FREQ	UNITS	MIN	TYP
Output Power at 1dB Compression Vds=8.0V lds=0.7xIDSS	P1dB	18 GHz	dBm		21.0
Saturated Power Vds=8.0V lds=0.7xIDSS	Psat	18 GHz	dBm		24.0
Output Third Order Intercept Point Vds=8.0V lds=0.7xIDSS	OIP3	18 GHz	dBm		29.0
Small Signal Gain Vds=8.0V lds=0.7xIDSS	SSG	18 GHz	dB		14.0
Power Added Efficiency at P1dB Vds=8.0V lds=0.7xIDSS	PAE	18 GHz	%		45

Note: Ids should be between 40% and 80% of Idss. Currently, our data shows Ids at 70% of IDSS. Low Ids will improve efficiency, but high Ids will make Psat and IP3 better.


## DC Specifications: at Ta= 25 °C

PARAMETERS & C	CONDITIONS	SYMBOL	UNITS	MIN	TYP	MAX
Saturated Drain Current Vds= 3.0 V Vgs= 0.0 V		IDSS	mA	70		90
Transconductance Vds= 2.5 V Vgs= 0.0 V		Gm	mS		100	
Pinch-off Voltage Vds= 3.0 V lds= 1.0 mA		Vp	V		-0.8	-1.0
Gate-to-Source Breakdown Voltage lgs= -0.3 mA		BVGSO	V		-18.0	
Gate-to-Drain Breakdown Voltage lgd= -0.3 mA		BVGDO	V		-18.0	
Chip Thermal Resistance Chip & 71 pkg 70 & 73 pkg		Rth	C/W		120 290*	


<sup>\*</sup> Overall Rth depends on case mounting



#### MwT-PH33F, Po, Gain & PAE vs Pin at 18GHz Vds=8V; Idq=0.7xIDSS



#### MwT-PH33F, OIP3 vs Po/tone with different Idq









# 26 GHz Medium Power AlGaAs/InGaAs pHEMT

## MwT-PH33F DUAL BIAS





# **Absolute Maximum Rating**

Symbol	Parameter	Units	Cont Max1	Absolute Max2
VDS	Drain to Source Volt.	٧	8.0	8.5
Tch	Channel Temperature	°C	+150	+175
Tst	Storage Temperature	°C	-65 to +150	+175
Pin	RF Input Power	mW	100	150

#### Notes

- 1. Exceeding any one of these limits in continuous operation may reduce the mean-time- to-failure below the design goal.
- 2. Exceeding any one of these limits may cause permanent damage.



# MwT-PH33F

## 26 GHz Medium Power AlGaAs/InGaAs pHEMT

## **S-Parameters**

Freq.	S	S11		S21		S12		S22		GMAX
GHz	dB	Ang (°)	dB	Ang (°)	dB	Ang (°)	dB	Ang (°)		dB
1	-0.183	-25.327	17.604	162.275	-37.987	76.340	-1.596	-6.660	0.106	27.795
2	-0.539	-48.599	16.930	146.469	-32.388	65.878	-1.893	-12.246	0.165	24.659
3	-1.016	-69.359	16.047	132.480	-29.751	55.469	-2.193	-17.309	0.248	22.899
4	-1.394	-87.173	15.102	120.450	-28.324	49.112	-2.464	-21.063	0.295	21.713
5	-1.868	-101.895	13.924	110.509	-27.659	43.211	-2.944	-24.615	0.419	20.792
6	-2.211	-113.757	12.993	102.137	-27.167	40.493	-3.081	-27.206	0.488	20.080
7	-2.539	-125.936	12.063	94.018	-26.779	37.723	-3.291	-29.596	0.580	19.421
8	-2.549	-135.590	11.348	86.930	-26.655	34.777	-3.340	-33.721	0.598	19.001
9	-2.671	-145.720	10.256	79.616	-26.645	34.484	-3.780	-35.765	0.751	18.451
10	-2.676	-153.374	9.705	73.468	-26.404	33.187	-3.609	-39.827	0.719	18.054
11	-2.595	-161.377	9.078	66.705	-26.506	33.582	-3.827	-41.951	0.783	17.792
12	-2.599	-167.847	8.369	61.321	-26.484	35.048	-3.853	-45.874	0.822	17.42
13	-2.603	-173.696	7.723	55.622	-26.483	35.639	-3.957	-49.609	0.896	17.103
14	-2.558	-179.318	6.999	50.263	-26.530	37.922	-3.985	-53.365	0.954	16.764
15	-2.490	175.476	6.548	45.300	-26.380	40.518	-4.064	-57.151	0.955	16.464
16	-2.494	170.999	6.070	40.875	-26.200	43.885	-3.976	-61.013	0.949	16.135
17	-2.511	166.967	5.476	35.956	-25.851	46.720	-3.930	-65.756	0.961	15.664
18	-2.303	162.920	4.897	31.857	-25.542	49.944	-3.865	-70.002	0.870	15.220
19	-2.272	161.235	4.450	27.655	-24.949	53.361	-3.844	-73.382	0.823	14.700
20	-2.248	155.053	4.057	23.089	-24.414	55.553	-3.993	-78.093	0.826	14.236
21	-2.178	152.324	3.543	16.206	-23.660	56.804	-3.783	-82.573	0.709	13.601
22	-2.200	149.391	3.061	12.687	-23.036	59.864	-3.727	-87.325	0.695	13.048
23	-1.910	147.069	2.643	8.442	-22.244	62.581	-3.685	-92.843	0.522	12.444
24	-1.938	143.894	2.178	3.482	-21.417	63.031	-3.730	-98.397	0.519	11.798
25	-1.982	140.780	1.659	-0.696	-20.838	61.265	-3.566	-103.955	0.505	11.249
26	-1.878	138.412	1.207	-4.718	-20.129	61.166	-3.462	-109.217	0.428	10.668
27	-1.711	135.244	0.747	-8.956	-19.558	60.255	-3.344	-114.074	0.337	10.15
28	-1.586	134.542	0.368	-12.927	-18.714	59.563	-3.233	-119.935	0.237	9.541
29	-1.635	130.710	-0.166	-17.261	-17.896	58.376	-3.120	-125.497	0.237	8.865
30	-2.277	205.120	-1.877	-33.900	-18.812	57.331	-4.035	-122.051	0.654	8.468

#### **ORDERING INFORMATION:**

When placing order or inquiring, please specify wafer number, if known. For details of Safe Handling Procedure please see supplementary information in available PDF on our website <a href="www.mwtinc.com">www.mwtinc.com</a>. For package information, please see supplementary application note in PDF format by clicking located on our website.

#### **Available Packaging:**

70 Package - MwT-PH33F70 71 Package - MwT-PH33F71 73 Package - MwT-PH33F73