
	- m		0	▫ >	
	ØS				
	Keying Shown as example				
 CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum -Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories -Temperature Range : -65°C to +175°C -Salt Spray : 2000 hours 	DimNominalØS35.7 MaxZ'31.5 MaxVV THREADM25x1-6g	A 14-10-2016 ISS DATE Designed By: TITLE	Latest modification - by Date:	ch does not comply with the Parties or by a third party on, technical notice.) Jurisdiction & Control List Not Listed	MOD N°
BASIC SERIES: 8D 5 - 17 J SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 17	20 B B ORIEN	SCALE NA	General linear Tolerances: ± WWW.SOURIAU.CC SOURIAU I	DM NPRDS / PROJECT 859 This document is the pr SOURIAU it must not be reprod communicated without p	uced or

	Ξ	۵	<u>п</u>	m		0
4		Contact Layout 20* • • • • • • 4# 12 16#22D				
60	Ctc A B C D 1 2 3 4 5 6 7 8 9 10	17-20 X Y 0 5.51 3.17 0 0 -5.51 -3.17 0 4.16 7.06 4.29 4.29 7.11 4.03 8.05 1.4 8.05 -1.4 7.11 -4.03 4.29 -4.29 4.16 -7.06 -4.16 -7.06 -4.29 -4.29				SOURIAU shall not be liable for a due to a use of the Products w the Specifications issued by either (professional recommend
22	11 12 13 14 15 16	-7.11 -4.03 -8.05 -1.4 -8.05 1.4 -7.11 4.03 -4.29 4.29 -4.16 7.06			A 14-10-20 ISS DATE Designed By: TITLE SCALE NA SOURIAN	Date: Comp General linear Tolerances: ±
	Н	G	F	E	FORMAT A3 D	SOURIAU 8D517.



Þ

σ