Ξ	۵	н <b>г</b>	m			0	Ξ		
		ØS							
<del>م</del> ن						LAYOUT SHOWN AS	EXAMPLE		
		Keying Sho	wn as example						
CHARACTERISTICS			Connector dimension						
-Standard : Based on	MIL-DTL-38999 Series III		Dim Nomi						
-Shell Material -Shell Plating -Insulator -Contacts	Shell Plating : Olive drab Cadmium Z 31 Max   Insulator : Thermoplastic VV THREAD M34x1-6g   Contacts : Copper Alloy : Copper Alloy				SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)				
-Seals & Grommet -Contact Plating	: Silicon Elastomer : Gold over copper Alloy 0.8µm mini	imum				Coun		n & Control List t Listed	
-Durability : 500 Mating cycles -Delivered without Souriau contacts					PN: 8D523W53PDL				
-Temperature Range	-				A 07-10-2016	First Release			
-Salt Spray Mass	: 500 hours : 41.49 g ± 10%				ISS DATE Designed By:	Latest modification - by Date:	CU	STOMER DRAWING	MOD N°
					TITLE	TITLE Aluminium Plug 8D series			
BASIC SERIES:		3 W 53 P D		ered W/O Contacts	SCALE	General linear Tolerances:	1	NPRDS / PROJECT 859	
CONTACT TYPE : Standard Crimp Contact ORIENTATION : D					SOURIAU     This document is the property of SOURIAU       it must not be reproduced or			d or	
SHELL SIZE : 23		┘ │ └──		: PIN(500 Matings)	FORMAT SOURIAU DRG N°				
PLATING : W =	Olive drab Cadmium		CONTA	CT LAYOUT : 23-53	A3				SHEET
							53PDL-C		1/2

-	Ŧ	۵	וד	m		0
		Contact Layout				
4	- <u></u>	$\begin{array}{c} \begin{array}{c} & & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ \end{array} \begin{array}{c} & & & & & & \\ & & & & \\ & & & & & \\ & & & & \\ & & & & & \\ & & & & & \\ & & & & \\ & & & & & \\ & & & & \\ & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & & & \\ & & & &$				
	B + 225 (5.72) C + 336 (9.53) D + 450 (11.43) E + 450 (11.43) F + 450 (11.43) G + 336 (9.53) H + 225 (5.72) J - 225 (5.72)	Y-axis (mm)     Contact position ID     X-axis (mm)     Y-axis (mm)       +455 (115.6)     £     -225 (5.72)     -260 (6.60)       +390 (9.91)     £     -336 (8.53)     -195 (4.95)       +326 (8.26)     £     -336 (8.53)     -065 (1.65)       +130 (3.30)     ħ     -336 (8.53)     +085 (1.65)       +000 (0.00)     k     -336 (8.53)     +085 (1.65)       -130 (3.30)     m     -225 (5.72)     +260 (6.60)       -325 (8.26)     n     -112 (2.44)     +325 (8.26)       -410 (10.41)     p     +000 (0.00)     +225 (6.26)				
ω	M    450 (11.43)       N    450 (11.43)       P    336 (8.53)       R    225 (5.72)       S    112 (2.84)       T     +.000 (0.00)       U     +.112 (2.84)	-130 (3.30)     s     +225 (5.72)     +1000 (0.00)       +000 (0.00)     1     +225 (5.72)     +130 (3.30)       +131 (3.30)     u     +112 (2.84)     -195 (4.95)       +325 (8.26)     y     +000 (0.00)     -280 (6.60)       >390 (9.91)     w     -112 (2.84)     -115 (4.95)       +455 (11.56)     x     -225 (5.72)     +130 (3.0)       +390 (9.91)     y     -225 (5.72)     +000 (0.00)       +325 (8.26)     z     -225 (5.72)     +000 (0.00)       +326 (6.60)     AA     -112 (2.84)     +195 (4.95)       Contacts     Contacts     Location       V_avis     Contact     Y_avis				
	ID     (mm)       W     +.336 (8.53)       X     +.336 (8.53)       Y     +.336 (8.53)       Z     +.336 (8.53)       a     +.225 (6.72)       JL     +.112 (2.84) <u>c</u> +.000 (0.00)       d    112 (2.84)       Shell     Arrangement     Num       size     no.     con	(mm)     (mm)     (mm)       +195 (4.95)     BB     +000 (0.00)     +130 (3.30)       +056 (1.65)     CC     +112 (2.84)     +065 (1.65)       -066 (1.65)     DD     +.112 (2.84)     -066 (1.65)       -260 (6.05)     EE     +000 (0.00)     -130 (3.30)       -260 (6.00)     FF    112 (2.84)     -066 (1.65)       -326 (0.60)     FF    112 (2.84)     -065 (1.65)       -330 (9.91)     HH     +000 (0.00)     +.000 (0.00)       -325 (2.62)				SOURIAU shall not be liable for an due to a use of the Products wi the Specifications issued by either o
N						(professional recommenda Countr FR PN: 8D523W
					A 07-10-20 ISS DATE Designed By:	16 First Release Latest modification - by Date:
-					SCALE NA	Alumin General linear Tolerances:
					SOURIA	
					FORMAT A3	SOURIAU 8D523W
L	Н	G	F	E	D	C

