ſ	I	۵	П	m	D		0
4 3	R 22.6 Max	N Thread					
			Keying Shown as	example			
	CHARACTERISTICS -Standard : Based on MIL-DTL-38999 -Shell Material : Stainless St -Shell Plating : Nickel -Insulator : Thermopla -Contacts : Copper Alle -Seals & Grommet : Silicon Elas	teel stic Dy		Connector dimension           Dim         Nominal           A         58.7±0.3           B         42.85+0.1/-0.15           R         32.5Max           S         55.6±0.4           W         3+0.9/-0.1           VV THREAD         M37x1-6g			SOURIAU sha due to a us the Specificatio (profes
N	-Contact Plating: Gold over of-Durability: 500 Mating-Delivered with Souriau contacts and-Temperature Range: -65°C to +2-Salt Spray: 500 hours	Accessories	m			A 04-10-2016 SS DATE	First Release Latest modifica Dat
4	BASIC SERIES: SHELL TYPE : Jam nut Receptacle CONTACT TYPE : Standard Crimp C SHELL SIZE : 25 PLATING : S = Nickel	8D 7 - 25 Contact	S 11 A N	ORIEI CONTACT TYPE : PIN(5 CONTACT LAY	00 Matings)	TITLE SCALE NA SOURIAU FORMAT	- - 
			I			A3	

G F

Н

С


 $\mathbf{\mathbf{n}}$ 

D

Е


σ	A				
		4			
LAYOUT SHOWN AS EXAMPLE		3			
all not be liable for any non-conformity or damage use of the Products which does not comply with ons issued by either of the Parties or by a third party essional recommendation, technical notice.) <u>Country</u> Jurisdiction & Control List FR Not Listed PN: 8D725S11AN					
ation - by MOD N° te: CUSTOMER DRAWING Stainless Steel Receptacle 8D series					
General linear       NPRDS / PROJECT         Tolerances:       859         ±       This document is the property of SOURIAU         V.SOURIAU.COM       it must not be reproduced or communicated without permission					
SOURIAU DRG N° 8D725S11AN-C	>	SHEET 1/2			
I B	I A				

	ت T	т п		_
	Contact Layout		Panel cutout	
			JAM NUT RECEPTACLE (TYPE 7)	
4				4
	Contacts (Insert arrangement 25-11)           Contact position ID         Location         Contact position ID         Contact (mm)         Contact position ID         Location           A        000 (0.00)         +.431 (10.95)         G        431 (10.95)         +.000 (0.00)           B         +.304 (7.72)         +.304 (7.72)         H        304 (7.72)         +.304 (7.72)           C         +.431 (10.95)        304 (7.72)         H        304 (7.72)         +.304 (7.72)           D         +.304 (7.72)        304 (7.72)         K         +.002 (2.34)        160 (4.06)           E         +.000 (0.00)        431 (10.95)         L        092 (2.34)        160 (4.06)           F        304 (7.72)        304 (7.72)		ØC	
ى ع	NOTES:         1. All dimensions are true position.         2. Front face of pin insert shown.         Shell       Arrangement no.       Number of contacts       Size rating       Contact location         25       -11       9       10       N       A,B,C,D,E,F,G,H,J         25       -11       2       20       N       A,B,C,D,E,F,G,H,J		DimNominalB43.43+0/-0.25ØC44.7+0.25/-0	3
	_			
			SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)	
N			CountryJurisdiction & Control ListFRNot Listed	2
			PN: 8D725S11AN	
			A 04-10-2016 First Release	
			ISS     DATE     Latest modification - by     MOD N°       Designed By:     Date:     CUSTOMER DRAWING	
			TITLE     Stainless Steel Receptacle 8D series	
			SCALE     General linear     NPRDS / PROJECT       NA     ±     859	_
_			NA     ±     DSS       SOURIAU     WWW.SOURIAU.COM     This document is the property of SOURIAU it must not be reproduced or communicated without permission	1
			FORMAT SOURIAU DRG N° SHEET	
	H G	F E	A3 8D725S11AN-C 2/2 D C B A	



	Contacts (Insert arrangement 25-11)					
		ation		Location		
Contact position ID	X-axis	Y-axis	Contact position ID	X-axis	Y-axis	
position ib	(mm)	(mm)	position ib	(mm)	(mm)	
Α	+.000 (0.00)	+.431 (10.95)	G	431 (10.95)	+.000 (0.00)	
В	+.304 (7.72)	+.304 (7.72)	н	304 (7.72)	+.304 (7.72)	
С	+.431 (10.95)	+.000 (0.00)	J	+.000 (0.00)	+.102 (2.59)	
D	+.304 (7.72)	304 (7.72)	К	+.092 (2.34)	160 (4.06)	
E	+.000 (0.00)	431 (10.95)	L	092 (2.34)	160 (4.06)	
F	304 (7.72)	304 (7.72)				

	Shell size	Arrangement no.	Number of contacts	Size contacts	Service rating	Contact location
	25	-11	9	10	N	A,B,C,D,E,F, G,H,J
			2	20		L,K



	0		₿	A			
	Panel cutout	сс И				4	
	Dim         Nominal           B         43.43+0/-0.           ØC         44.7+0.25/	.25				3	
	SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) $\frac{Country \qquad Jurisdiction \& Control List \\ \hline FR \qquad Not Listed}$ <b>PN: 8D725S11AN</b>						
)16	16     First Release     MOD N°       Latest modification - by     MOD N°       Date:     CUSTOMER DRAWING						
	Stainle	ess Steel F	Recepta	cle 8D series			
-	Toler	al linear ances: :		NPRDS / PROJECT <b>859</b>		1	
U	U WWW.SOURIAU.COM			This document is the pro SOURIAU it must not be reproduc communicated without pe	ced or		
	SOURIAU DRG N° SHEET 8D725S11AN-C 2/2						
	C		В	A	1	J	

