
D	т г	m	D	0			
	ØS				OWN AS EXAMPLE		
	Keying Shown a			LATOUT SH	IOWN AS EXAMPLE		
CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8μm minimum -Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories -Temperature Range : -65°C to +175°C -Salt Spray : 2000 hours -Mass : 39.3 g ± 10%		Connector dimensionDimNominalØS35.7 MaxZ'31.5 MaxVV THREADM25x1-6g	A 14-10-201 ISS DATE Designed By:	due to a use of the P the Specifications issued I (professional rec PN: 8	SD517J35BN	nply with y a third party otice.) iction & Control List Not Listed CUSTOMER DRAWING	MOD N°
BASIC SERIES: 8D 5 - 17 J SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 17	J 35 B N	ORIENTAT CONTACT TYPE : SOCKET(500 N CONTACT LAYOUT	Matings)	J WWW.SOU	Composite Plug 80 eral linear erances: ± RIAU.COM JRIAU DRG N°	D series NPRDS / PROJECT 859 This document is the prope SOURIAU it must not be reproduced communicated without perm	d or

	Ξ	۵	П	m	U	0	
4	-	Contact Layout					
	2312 (7.92) 3312 (7.92) 4242 (6.15) 5234 (5.94)	Contacts (Insert arrangement 17-35) n Contact position ID Location Y-axis (mm) 000 (0.00) 094 (2.39) 094 (2.39) 31 .000 (0.00) 184 (4.67) +.221 (5.61) 32 088 (2.26) +.316 (8.03) +.131 (3.33) 33 +.078 (1.98) +.221 (5.61) 049 (1.24) 35 +.078 (1.98) +.214 (1.61)					
ى ى	$\begin{array}{rrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrr$	-139 (3.53) 36 +.078 (1.98)049 (1.24) -229 (5.82) 37 +.078 (1.98)139 (3.53) +279 (7.09) 38 +.078 (1.98)229 (5.82) +176 (4.47) 39 +.078 (1.98)229 (5.82) +176 (4.47) 39 +.078 (1.98)229 (5.82) +004 (0.10) 41 +.156 (3.96) +.176 (4.47) -094 (2.39) 42 +.156 (3.96) +.176 (4.47) -184 (4.67) 43 +.156 (3.96)004 (0.10) -274 (6.99) 44 +.156 (3.96)004 (0.10) -274 (6.99) 44 +.156 (3.96)094 (2.39) +.316 (8.03) 45 +.156 (3.96)184 (4.67) +.221 (5.61) 46 +.156 (3.96)274 (6.96) (Insert arrangement 17-35) n Location					
	position ID X-axis (mm) 19 078 (1.98) 20 078 (1.98) 21 078 (1.98) 22 078 (1.98) 23 078 (1.98) 24 078 (1.98) 25 .000 (0.00) 26 .000 (0.00) 27 .000 (0.00) 28 .000 (0.00) Shell Arrangement no. Nu	Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) +.131 (3.33) 47 +.242 (6.15) +.221 (5.61) +.041 (1.04) 48 +.242 (5.94) +.131 (3.33) 049 (1.24) 49 +.234 (5.94) +.131 (3.33) 049 (1.24) 49 +.234 (5.94) +.131 (3.33) 049 (1.24) 49 +.234 (5.94) 041 (1.04) 239 (5.82) 51 +.234 (5.94) 044 (1.24) 239 (5.82) 51 +.234 (5.94) 139 (3.53) 319 (3.05) 52 +.234 (5.94) 229 (5.82) 319 (3.610) 52 +.234 (5.94) 229 (5.82) 312 (7.92) 004 (0.10) +.176 (4.47) 54 +.312 (7.92) 004 (2.03) 004 (0.10) mber of stacts Stervice Contacts Supersed stats contacts rating location	es			SOURIAU shall not be lia due to a use of the Po the Specifications issued b (professional reco	roducts w by either (
2			~			PN: 8	Count FR D517
					ISS DATE Designed By:	Date:	
-					SCALE NA	Gene Tole	Comp eral linear erances: ±
		0	F	E	FORMAT A3	SOL 8D	JRIAU.
	Н	G		E		C	I



ω