

Data Sheet HD-EM0803-LW20-R

PUI Audio's 8mm diameter by 3mm thick **HD-EM0803-LW20-R** is an eccentric rotating mass vibration haptic motor. Originally designed for use in pagers/beepers, this device is great for use in wearables for haptic feedback.


### **Features:**

- Driven with positive or negative DC for clockwise or counterclockwise movement
- Convenient 20mm lead wires for simple electrical connection
- 12,000 RPMs with 3 VDC input

**Specifications** 

Parameters	Values	Units
Rated Voltage	3	VDC
Operating Voltage Range	2.4 ~ 3.6	VDC
Terminal Resistance	38 ±50%	Ohms
Rated Speed (at 3 VDC)	12,000 ±3,000	RPMs
Current Draw (at 3 VDC)	80	mA
Stall Current Draw	130	mA
Insulation Resistance	1	MOhms
Acoustic Noise (Max)	50	dBA
Housing Material	SPC	-
Acceptable Soldering Methods	Hand Solder	-
Environmental Compliances	RoHS	-
Weight	1	Grams
Storage Temperature	-40 ~ +85	°C
Operating Temperature	-20 ~ +60	°C

### **Measurement Methods**




Specification of the dummy Jig
 Size: 45mm x 105mm x 15mm

Weight : 100grMaterial : Bakelite

· Vibration motor should be attached by using a double-sided tape

# Acoustic noise




**Reliability Testing** 

Type of Test	Test Specifications
High Temperature Test	96 hours at 80°C
Low Temperature Test	96 hours at -40°C
H2S Corrosion Resistance Test	Concentration: 3 ±1 PPM Test Environment: 40°C, humidity 80% RH Test Duration Time: 240 hours
	Temperature: -40°C to +85°C
	Test Duration: 30 minutes
Temperature Cycle Testing	Test Cycles: 15 cycles
Vibration Test	3mm deflection at 1000 cycles per minute, for 10 minutes in each axis (X, Y, Z).
	Weight: 150g (including motor)
	Drop Height: 150cm
	Floor Material: Steel
	Direction: ±X, ±Y, ±Z; total 6 faces
Drop Test	Number of Times: Each face 3 Times
	60,000 operating cycles in room temperature
Load Test	Cycle test condition: 2 seconds on, 2 seconds off

Acceleration, resistance, rated current and noise must meet specifications after allowing the device to rest for 4 hours after test.

## **Dimensions**



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2021, PUI Audio Inc.

**Specifications Revisions** 

Revision	Description	Date
A	Released from Engineering	4/6/2021

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- ${\bf 2.} \quad {\bf Specifications \ subject \ to \ change \ or \ with drawal \ without \ notice.}$