Г	т <u>О</u> т т		0	₿ >		
4	Z Market Constrained of the second of the s				4	
ω			LAYOUT SHOWN AS EXAM	IPLE	3	
	Keying Shown as example					
	CHARACTERISTICS Connector dimension					
	-Standard : Based on MIL-DTL-38999 Series III ØS 44.9 Max	[_	
N	-Shell Material : Aluminium -Shell Plating : Olive drab Cadmium -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8μm minimum		SOURIAU shall not be liable for any no due to a use of the Products which the Specifications issued by either of the (professional recommendation, Country FR	does not comply with Parties or by a third party	2	
	-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories		PN: 8D523W55AE			
	-Temperature Range : -65°C to +175°C	A 07-10-2016	First Release			
	-Salt Spray : 500 hours -Mass : 49.66 g ± 10%	ISS DATE	Latest modification - by		MOD N°	
	-Wass . 45.00 g ± 10/0	Designed By:	Date:	CUSTOMER DRAWING		
		TITLE	Aluminiur	n Plug 8D series		
	BASIC SERIES: 8D 5 - 23 W 55 A E SHELL TYPE : Plug with RFI Shielding - - 23 W 55 A E	SCALE .	General linear Tolerances:	NPRDS / PROJECT 859		
	CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 23 CONTACT TYPE : PIN(500 Matings)			This document is the property SOURIAU it must not be reproduced o communicated without permis	or	
	PLATING : W = Olive drab Cadmium CONTACT LAYOUT : 23-55		SOURIAU D	RG N°	SHEET	
		A3	8D523W55		1/2	
	H G F E	D	С	B A		

ſ	Ŧ	۵ ا	н т	m	D	0	
		Contact Layout					
4	-XL N	$\begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} $					
	B +.225 (5.72) C +.336 (8.53) D +.450 (11.43)	Contacts (Inset arrangement 23-55) On Contact position ID Location Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) +455 (11-56) f -112 (2.84) -325 (8.26) +320 (8.26) h -336 (8.53) -195 (4.95) +130 (3.30) i -336 (8.53) -065 (1.65) -130 (3.00) J -336 (8.53) +055 (1.95) -325 (8.26) m -225 (5.72) +260 (6.60) -326 (8.26) m -225 (5.72) +260 (6.60) -326 (9.94) n -325 (8.26) -326 (2.44) +325 (8.26) -326 (9.94) n -225 (5.72) +260 (6.60) -390 (9.94) -326 (8.26) -330 (9.94) n -112 (2.84) +325 (8.26) +325 (8.26) +325 (8.26) +326 (8.26) +326 (8.26) +326 (8.26) +326 (8.26) +330 (8.35) +356 (1.45) +326 (8.26) +330 (8.35) +356 (8.26) +360 (8.00) +260 (6.00) +360 (8.00) +366 (8.60) +360 (8.60) +360 (8.60) +360 (8.					
ω	K 112 (2.84) L 225 (6.72) M 336 (8.53) N 450 (11.43) P 450 (11.43) S 336 (8.53) T 225 (6.72) U 112 (2.84) V +.000 (0.00) W +.112 (2.84) X +.225 (6.72) Y +.336 (8.53)	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$					
	size no. con	ber of Size Service Contact Superseder tacts contacts rating location	5			SOURIAU shall not be liable for	an
						due to a use of the Products the Specifications issued by either (professional recomment	r o
N						Cou	nti R
						PN: 8D523	3\
					A 07-10-20 ISS DATE Designed By:	016 First Release Latest modification - by Date:	
					TITLE	Alum	
→					SCALE NA	General linear Tolerances:	
					SOURIA	U WWW.SOURIAU	.0
					FORMAT A3	SOURIA 8D523\	
L	Н	G	F	E	D	C	

	Φ		A			
					4	
					3	
whic r of t datio ntry R	non-conformit th does not co he Parties or to n, technical no Jurisd	mply with by a third par	ty trol List		2	
		CUSTOME	R DRAWING	MOD N°		
inium Plug 8D series						
r	NPRDS / PROJECT					
859 This document is the property of						
.CC	.COM SOURIAU it must not be reproduced or communicated without permission					
	DRG N° 5AE-C	1		SHEET 2/2		
003	BAE-C		A	-, -		