



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2020AUG20
 © COPYRIGHT 2020 BY - ALL RIGHTS RESERVED.

| REVISIONS | | | | |
|-----------|-----|---------------------|-----------|---------|
| P | LTR | DESCRIPTION | DATE | APVD |
| 1 | | Preliminary Release | 20AUG2020 | JCL JCC |
| | | | | |
| | | | | |



| DEUTSCH PART NO. | SIZE | WIRE GAGE RANGE | RECOMMENDED STRIP LENGTH | CRIMP INFORMATION | |
|------------------|------|-----------------|--------------------------|-------------------------------|-------------------------------|
| | | | | TOOL | POSITIONER |
| 0641-24-2031 | 20 | 26, 28, 30 | .186 TO .216 | M22520/2-01 or M22520/7-01 | M22520/2-02 or M22520/7-02 |

1. MATERIAL: PIN COPPER ALLOY.
2. FINISH: .000050 MIN. GOLD PLATING PER MIL-G-45204 OVER NICKEL
3. DIMENSIONS ARE INCHES UNLESS OTHERWISE SPECIFIED.

| | | | | |
|---|--------|---------------------------------|---|----------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN J. CORONADO 2020AUG20 |  TE Connectivity | |
| DIMENSIONS: in | | CHK JC CAMPOS 2020AUG20 | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD JC CAMPOS 2020AUG20 | NAME CONTACT, CRIMP. PIN, SZ 20 FOR 26-30 AWG WIRE | |
| 0 PLC ±- 1 PLC ±.1 2 PLC ±.02 3 PLC ±.005 4 PLC ±.0005 ANGLES ±- FINISH | | PRODUCT SPEC - | SIZE A2 | |
| MATERIAL | NOTE 1 | APPLICATION SPEC - | CAGE CODE 11139 | DRAWING NO 0641-24-2031 |
| NOTE 2 | | WEIGHT - | RESTRICTED TO - | SCALE 25:1 |
| CUSTOMER DRAWING | | | SHEET 1 | REV 1 |