	I	G	П	т			0			A			
4		M Thread	ØS								4		
ယ	LAYOUT SHOWN AS EXAMPLE												
	Keying Shown as example												
	CHARACTERISTICS			Connector dimension Dim Nominal									
N	-Standard : Based on MIL-DTL-38999 S -Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplase -Contacts : Copper Allow -Seals & Grommet : Silicon Elaste -Contact Plating : Gold over composition -Durability : 500 Mating -Delivered with Souriau contacts and and	tic y omer opper Alloy 0.8µm minimum cycles	<u> </u>	ØS 48 Max Z' 31.5 Max HREAD M37x1-6g			due to a use the Specification (profess	e of the Products which o	e Parties or by a third party technical notice.) Jurisdiction & Control List Not Listed		2		
	-Temperature Range : -65°C to +20 -Salt Spray : 2000 hours					A 07-10-2016 First Release							
	-Mass : 80.4 g ± 10%					ISS DATE Designed By:	Latest modificat		CUSTOMER DRAWIN	MOD N°			
						TITLE		Composite	e Plug 8D series				
	BASIC SERIES: SHELL TYPE : Plug with RFI Shielding	8D 5 - 25 N	1 37 B A			SCALE NA		General linear Tolerances: ±	NPRDS / PROJECT 859		-		
	CONTACT TYPE : Standard Crimp Co	ontact		SOURIA	U WWW.SOURIAU.COM it must not be reproduce communicated without per			J roduced or	_				
	PLATING : M = Nickel			CONTACT TYPE : SOCKET(500 CONTACT LAYO		FORMAT A3		SOURIAU DRG N° 8D525M37BA-C			-		
L	Н	G	F	E	7	D	C	/ נואוכבכעס	BA-C	1/2 A			

ſ	т		Q		П	ш			J	C		σ		A		
		Contact L	ayout													
4	-X R															4
	position X-axis		nt 25-37)	/-axis												
ω	ID (mm) A +.000 (.00) B +.185 (4.70) C +.333 (8.46) D +.441 (11.20) E +.500 (12.70) G +.441 (11.20) H +.333 (8.46) J +.186 (4.72) K +.000 (.00) L 186 (4.72) M 333 (8.46) N 441 (11.20) P 500 (12.70) S 441 (11.20) T 333 (8.46) U 186 (4.72) K +.000 (.02)	(mm) P0: +472 (11.99) +472 (11.99) +382 (9.70) +249 (6.32) +086 (2.18) -249 (6.32) +382 (9.70) -472 (11.99) -472 (11.99) -472 (11.99) -382 (9.70) -249 (6.32) +266 (2.18) +266	(mm) W +242 (6.15) +2.2 X +326 (8.28) +0.0 Y +326 (8.28) -0.0 Z +.242 (6.15) -2 a +0.96 (2.18) -3.3 b -0.96 (2.18) -3.3 c 242 (6.15) -2 d 326 (8.28) -0.0 e 326 (8.28) -0.0 e 326 (8.28) -0.0 f 242 (6.15) +2.2 g 086 (2.18) +3.3 h +.000 (.00) +1.1 k +.154 (3.91) -0.0 m +.154 (3.91) -0.0 n +.000 (.00) -1.1 p 154 (3.91) -0.0 q 154 (3.91) -0.0 r +.000 (.00) -1.1	mm) 36 (5.99) 36 (2.18) 36 (2.18) 36 (2.18) 36 (5.99) 20 (8.13) 20 (8.13) 26 (5.99) 36 (2.18)												3
										due to the Specific	shall not be liable fo a use of the Product ations issued by eith ofessional recomme	ts which does not co er of the Parties or l	mply with by a third party			
N												ountry Jurisc FR	liction & Contro Not Listed	l List		2
											PN: 8D52	5M37BA				
									A 07-10-2	2016 First Release						-
									ISS DAT		fication - by Date:		CUSTOMER D		MOD N°	
									Designed By: TITLE			nposite Plug 8		rawing		
									SCALE		General line		NPRDS / PF			_
									NA	$\square \bigcirc \bigcirc$	Tolerance: ±		859			1
									SOURI	AU WV	VW.SOURIA	J.COM	it must no	ent is the prope SOURIAU ot be reproduced ed without pern	d or	
									FORMAT		SOURI	AU DRG N°			SHEET	
						 _	ľ	7	A3			M37BA-C	I		2/2	
	Н		G		F	E		/	D	C)	В		А		