

HCM1A0703V2

Automotive grade high current power inductors



Product features

- AEC-Q200 qualified
- High current carrying capacity
- Magnetically shielded, low EMI
- DC-DC converter applications up to 1 MHz
- Filtering applications up to Self Resonant Frequency (SRF) [See product specification table]
- Inductance range from 0.10 μ H to 33 μ H
- Current range from 1.6 A to 54 A
- 7.3 mm x 6.8 mm footprint surface mount package in a 3.0 mm height
- Moisture Sensitivity Level (MSL): 1
- Alloy powder core material

Applications

- Body electronics
 - Central body control module
 - Vehicle access control system
 - Headlamps, tail lamps and interior lighting and LED lighting
 - Heating ventilation and air conditioning controllers (HVAC)
 - Doors, window lift and seat control
- Advanced driver assistance systems
 - 77 GHz radar system
 - Adaptive cruise control (ACC)
 - Automatic parking control
 - Collision avoidance system/ Car black box system
- Infotainment and cluster electronics
 - Active noise cancellation (ANC)
 - Audio subsystem: head unit and trunk amp
 - Digital instrument cluster
 - In-vehicle infotainment (IVI) and navigation
 - Port power/USB HUB for front and rear passengers
- Chassis and safety electronics
 - Airbag control unit
 - Electronic stability control system (ESC)
- Engine and Powertrain Systems
 - Electric pumps, motor control and auxiliaries
 - Powertrain control module (PCU)/ Engine Control unit (ECU)
 - Transmission Control Unit (TCU)

Environmental data

- Storage temperature range (Component): -55 °C to +155 °C
- Operating temperature range: -55 °C to +155 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant



Powering Business Worldwide


Product specifications

Part number ⁶	OCL ¹ (μH) $\pm 20\%$	FLL ² (μH) minimum	I_{rms}^3 (A)	I_{sat}^4 (A)	DCR (m Ω) typical @ +20 °C	DCR (m Ω) maximum @ +20 °C	SRF (MHz) typical	K-factor ⁵
HCM1A0703V2-R10-R	0.10	0.064	29	54	0.63	0.8	350	1284
HCM1A0703V2-R15-R	0.15	0.090	24	30	1.03	1.3	195	1541
HCM1A0703V2-R22-R	0.22	0.130	18	32	1.8	2.3	150	1039
HCM1A0703V2-R33-R	0.33	0.210	15	19	2.9	3.5	95	823
HCM1A0703V2-R47-R	0.47	0.300	13	17	3.7	4.14	70	713
HCM1A0703V2-R56-R	0.56	0.350	13	12	3.8	4.5	60	805
HCM1A0703V2-R68-R	0.68	0.430	12	13	4.8	5.5	57	843
HCM1A0703V2-R82-R	0.82	0.520	10	14	5.7	6.6	55	608
HCM1A0703V2-1R0-R	1.0	0.64	10	9.0	6.5	7.8	48	627
HCM1A0703V2-1R2-R	1.2	0.76	9	12	8.6	9.9	35	434
HCM1A0703V2-1R5-R	1.5	0.96	8.5	10	9.5	11.5	35	445
HCM1A0703V2-2R2-R	2.2	1.40	7.0	8.5	12.5	15.5	29	532
HCM1A0703V2-3R3-R	3.3	2.10	5.0	7.5	24.5	28.5	25	281
HCM1A0703V2-4R7-R	4.7	3.00	4.0	6.8	40.3	46.5	20	227
HCM1A0703V2-6R8-R	6.8	4.30	3.6	5.6	54	65	16	276
HCM1A0703V2-8R2-R	8.2	5.20	3.5	4.8	53	64	14	173
HCM1A0703V2-100-R	10	6.40	3.3	4.4	65	75	12	177
HCM1A0703V2-150-R	15	9.60	2.6	3.6	96	110	9.5	147
HCM1A0703V2-220-R	22	14.1	2.0	2.9	135	149	7.0	134
HCM1A0703V2-330-R	33	19.8	1.6	2.3	200	242	6.5	92


1. Open Circuit Inductance (OCL) Test Parameters: 100 kHz, 0.25 V_{rms}, 0.0 Adc, +25 °C
2. Full Load Inductance (FLL) Test Parameters: 100 kHz, 0.25 V_{rms}, I_{sat}, +25 °C
3. I_{rms}: DC current for an approximate temperature rise of 30 °C without core loss. Derating is necessary for AC currents. PCB layout, trace thickness and width, air-flow, and proximity of other heat generating components will affect the temperature rise. It is recommended that the temperature of the part not exceed +155 °C under worst case operating conditions verified in the end application.

4. I_{sat}: Peak current for approximately 20% rolloff @ +25 °C
5. K-factor: Used to determine B_{p-p} for core loss (see graph). B_{p-p} = K * L * ΔI . B_{p-p}: (Gauss), K: (K-factor from table), L: (Inductance in μH), ΔI (Peak to peak ripple current in Amps).
6. Part Number Definition: HCM1A0703V2-xxx-R
HCM1A0703V2 = Product code and size
xxx= inductance value in μH , R= decimal point,
If no R is present then last character equals number of zeros
-R suffix = RoHS compliant


Dimensions (mm)



Recommended pad layout



Schematic




Part marking: 1AxxxV2, xxx=inductance value in μH , R=decimal point. If no R is present then last character equals number of zeros. xxxx=Lot code
All soldering surfaces to be coplanar within 0.1 millimeters
Tolerances are ± 0.3 millimeters unless stated otherwise
Pad layout tolerances are ± 0.1 millimeters unless stated otherwise
DCR measured from point "a" to point "b"
Do not route traces or vias underneath the inductor





Packaging information (mm)

Drawing not to scale







Supplied in tape and reel packaging, 2000 parts per 13" diameter reel



Core loss vs B_{p-p}




Core loss vs B_{p-p}




Core loss vs B_{p-p}


HCM1A0703V2-1R5-R




HCM1A0703V2-2R2-R




HCM1A0703V2-3R3-R




HCM1A0703V2-4R7-R



HCM1A0703V2-6R8-R




HCM1A0703V2-8R2-R




Core loss vs B_{p-p}


HCM1A0703V2-100-R




HCM1A0703V2-150-R









HCM1A0703V2-220-R









HCM1A0703V2-330-R









Inductance and impedance vs. frequency





Inductance and impedance vs. frequency







Inductance and impedance vs. frequency









Inductance and impedance vs. frequency









Inductance and temperature rise vs. current







Inductance and temperature rise vs. current



Inductance and temperature rise vs. current



Inductance and temperature rise vs. current



Solder reflow profile




Table 1 - Standard SnPb Solder (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) Free Solder (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T _{smin})	100 °C	150 °C
• Temperature max. (T _{smax})	150 °C	200 °C
• Time (T _{smin} to T _{smax}) (t _s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T _{smax} to T _p	3°C/ Second Max.	3 °C/ Second Max.
Liquidous temperature (T _L)	183 °C	217 °C
Time at liquidous (t _L)	60-150 Seconds	60-150 Seconds
Peak package body temperature (T _p)*	Table 1	Table 2
Time (t _p)** within 5 °C of the specified classification temperature (T _c)	20 Seconds**	30 Seconds**
Average ramp-down rate (T _p to T _{smax})	6 °C/ Second Max.	6 °C/ Second Max.
Time 25 °C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. 10911 BU-MC19047
April 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

