

PB6B2FM3M1CAL05 ✓ ACTIVE

Alcoswitch | Alcoswitch PB6

TE Internal #: 2329387-8

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Switch, Single Actuator, Flush Actuator Profile, Threaded, Alcoswitch PB6

[View on TE.com >](#)



Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Push Button Switch Product Type	Switch
Illuminated	With
Actuator Style	Round

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Momentary

Electrical Characteristics

Operating Voltage Range	32 VAC, 125 VAC
-------------------------	-----------------

Body Features

Actuator Force	306 – 612 g[10.8 – 21.6 oz]
----------------	-----------------------------



Case Material	Diallyl Phthalate (DAP)
Actuator Material	Polyamide
Product Orientation	Vertical
Actuator Profile	Flush
Bushing Style	Threaded
Bushing Thread Size	M12 x .75
Actuator Color	Red

Contact Features

Contact Current Rating	.12 A
Switch Contact Plating Material	Gold over Silver

Housing Features

Process Sealed	Yes
----------------	-----

Industry Standards

IP Rating	IP68
-----------	------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Alcoswitch PB6



Customers Also Bought



TE Part #2834006-2
RELEASE POKE-IN
CONNECTOR_2POLES



TE Part #1241050-6
2x6P MOD II BREAK AWAY HDR,SMD,
BLISTER



TE Part #1-1625885-9
1W SM M/OX 5% 12R



TE Part #1-2329387-4
PB OFF/ON FC YLW M1 TERM GRE
LED IP68



TE Part #2329359-7
PB ON/OFF HC RED M1 TERM IP68
500MM LHS



TE Part #2-1734839-0
FPC CONN. 0.5MM PITCH T/C,20P



TE Part #160631-3
SUB MINIATURE AMPLIVAR SPLICE

Documents

Product Drawings

[PB OFF/ON FC RED M1 TERM YLW LED IP68](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2329387-8_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2329387-8_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2329387-8_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[IP68 Sub Mini PB Data Sheet](#)

English