

Data Sheet HD-VA2527


### **Features:**

- Fast response times over a wide frequency range
- Maximum acceleration of 2.61 Gp-p measured at 65 Hz.
- Cylindrical form allows for a variety of implementations

**Specifications** 

Parameters	Values	Units
Input Voltage (@ 200 Hz)	1.0	$ m V_{rms}$
Max Voltage (@ 200 Hz)	3.0	$ m V_{rms}$
Power Consumption	0.04	W
Nominal Impedance DCR	5.7	Ohms
Acceleration Frequency (Max)	65	Hz
Vibration Acceleration	2.61	<b>Gp-</b> p
Rise Time 0-90%	< 80	ms
Fall time 100-10%	< 80	ms
Polarity	Acceleration generated to top side when input positive voltage into plus side pad.	-
Environmental Compliances	RoHS/REACH	-
Weight	28	Grams
Storage Temperature	-20 ~ +60	°C
Operating Temperature	0 ~ +50	°C

## **Vibration Acceleration**




**Reliability Testing** 


Reliability Testing			
Type of Test	Test Specifications		
	Temperature: +50°C		
High Temperature Test	Test Duration Time: 8 hours		
	Temperature: 0±2°C		
Low Temperature Test	Test Duration Time: 8 hours		
_	Temperature: 35°C		
	Relative Humidity: 90 to 95%		
Humidity Test	Test Duration Time: 8 hours		
	Run cycle shown 1 times		
Temperature Cycle Testing	1 cycle  +65°C  Humidity: 50%  +25°C  Humidity: 0%  2h 32h 32h 32h 32h 4h 6h		
Vibration Test	Test Axis: XYZ Test Repetition: 60 minutes per axis (30 minutes total)		
Drop Test	Sample with 200g Mass is dropped only one time for 6 surfaces onto P-tile from the 1.7m height		

Acceleration frequency characteristics shall be within tolerance after each test.

## **Dimensions**



# **Packaging**



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2022, PUI Audio Inc.

**Specifications Revisions** 

Revision	Description	Date
Α	RELEASED FROM ENGINEERING	07/20/2022

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .ssw
- 2. Specifications subject to change or withdrawal without notice.