

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
APPLICATION STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C							
	VOLTAGE	100 V AC							
	CURRENT	0.4 A							
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENT			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING			X	X
MARKING		CONFIRMED VISUALLY						X	X
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz)			45 mΩ MAX.			X	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA (DC OR 1000 Hz)			55 mΩ MAX.			X	-
INSULATION RESISTANCE		250 V DC			100 MΩ MIN.			X	-
VOLTAGE PROOF		300 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN			X	-
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE: 98 N MAX. WITHDRAWAL FORCE: 9.1 N MIN.			X	-
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm, - m/s ² FOR 2 h IN 3 DIRECTIONS.			1) NO ELECTRICAL DISCONTINUITY OF 1 μs 2) CONTACT RESISTANCE: 55 mΩ MAX. 3) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
SHOCK		490 m/s ² DURATION OF PULSE 11 ms FOR 3 TIMES IN 3 DIRECTIONS.						X	-
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) INSULATION RESISTANCE:			X	-
RAPID CHAGE OF TEMPERATURE		TEMPERATURE -55→+5~+35→+85→+5~+35°C TIME 30→10~15→30→10~15 min. UNDER 5 CYCLES.			100 MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO HEAVY CORROSION.			X	-
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA-38)						X	-
REMARKS									
				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				<i>M. Nagata</i>	<i>M. Nagata</i>	<i>H. Okawa</i>	<i>J. Yoshimura</i>		
UNLESS OTHERWISE SPECIFIED, REFER TO JIS C 5402.				01.04.06	01.04.06	01.04.06	01.04.06		
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST									
HS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO.		
							FX8 - 140S - SV (23)		
CODE NO.(OLD)		DRAWING NO.		CODE NO.				1	
CL		ELC4 - 150678 - 02		CL 578 - 0207 - 1 - 23				1	

FORM NO. 231-1

PC

TO
PCK