

### Main

|                              |   |
|------------------------------|---|
| Device short name            | G   |
| Enclosure type               | Standard environment enclosure indoor                       |
| Product Specific Application | Control electrically driven water pumps and air compressors |
| Range of Product             | Square D Pumptrol   |
| Switch application           | Reverse   |

### Complementary

|                                     |  |
|-------------------------------------|--|
| Approximate adjustable differential | 4...8 psi (27.58...55.16 kPa)  |
| Depth                               | 3.68 in (93.47 mm)   |
| Electrical connection               | Screw clamp terminal   |
| Fixing Mode                         | By brackets  |
| Fluid connection type               | 0.25 inch NPSF internal  |
| Height                              | 5.72 in (145.29 mm)  |
| Material                            | Zinc plated steel: flange  |
| Materials in contact with fluid     | Nitrile (Buna-N) diaphragm   |
| Maximum pressure                    | 100 psig   |
| Maximum Horse Power Rating          | 2 Hp 115 V AC, 1 phase<br>3 Hp 115 V AC, 3 phase<br>3 Hp 230 V AC, 1 phase<br>5 Hp 230 V AC, 3 phase<br>5 Hp 460/575 V AC, 1 phase<br>5 hp 460/575 V AC, 3 phase |
| Number of poles                     | 2  |
| Permissible voltage                 | 575 V AC   |
| Pressure actuator                   | Diaphragm  |
| Net Weight                          | 2.25 lb(US) (1.02 kg)  |
| Range on decreasing pressure        | 10...35 Psi (68.95...241.32 kPa)<br>5.5...30.5 psi (37.92...210.29 kPa)  |
| Scale type                          | Adjustable differential  |
| Switch function                     | DPST   |
| Width                               | 3.44 in (87.38 mm)   |

### Environment

|                           |  |
|---------------------------|--|
| NEMA Degree of Protection | NEMA 1   |
| Product Certifications    | UL listed file E12158 CCN NKPZ[RETURN]CSA file LR25490 |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1CP7G21536 |
| Discount Schedule | CP7G         |
| GTIN              | 785901776826 |
| Returnability     | No           |
| Country of origin | MX           |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 12.40 in (31.484 cm) |
| Package 1 Width              | 4.88 in (12.395 cm)  |
| Package 1 Length             | 31.48 in (79.969 cm) |
| Package 1 Weight             | 32.00 oz (907.185 g) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |