

REV. 1 10/10/95

COIL:

RESISTANCE	7500 OHMS ± 10%
NOMINAL VOLTAGE	115.0 VAC (60-400 Hz)
MUST OPERATE	66.0 VAC (60-400 Hz)
MUST RELEASE	7.0 VAC MIN. (60-400 Hz)


ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES:

OPERATE TIME	15 MS MAX.
RELEASE TIME	20 MS MAX.
CONTACT BOUNCE	5 MS MAX. (NC)
	2 MS MAX. (NO)

CUSTOMER DATA SHEET



CONTACT RATING:

10 AMPS 30 VDC RES.
10 AMPS 115 VAC 400 Hz, 6A 30 VDC
INDUCTIVE 100,000 OPERATIONS

DR. R.B. 6/26/95 | CK. *[Signature]*



CUST. HI-G  
CUST. NO. 2TR-2D-215

TYPE '07' RELAY

B07B945BZ1-8021