SC300A500FP

Hyde Park, Ultrasonic sensor, discrete, flat profile, 12 24 V DC



Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Superprox +
Device short name	SC300
Sensor design	Flat form
Type of sensing window	Configurable
Material	Plastic
Enclosure Material	ULTEM
Front material	Glass epoxy
Type of output signal	Discrete
Wiring Technique	4-wire
[Us] rated supply voltage	1224 V DC overload and short-circuit protection
Supply voltage limits	1028 V DC
Electrical connection	Cable, 9.84 ft (3 m)
Product Specific Application	Discrete proximity

Complementary

Maximum differential travel	0.03 in (0.7 mm)
Blind zone	0.25 in (6.4 mm)
Transmission frequency	500 kHz
Repeat accuracy	0.7 %
Beam angle	8°
Minimum size of detected object	Cylinder diameter 2.5 mm - up to 1 mm sensing distance
Current Consumption	25 mA
Maximum switching current	100 mA reverse polarity protection
Height	0.30 in (7.62 mm)
Width	0.75 in (19.05 mm)
Depth	0.30 in (7.62 mm)
Length	1.30 in (33.02 mm)
Net Weight	0.26 lb(US) (0.12 kg)

Environment

Product Certifications	UL	
Marking	CE	
NEMA degree of protection	NEMA 4X indoor use only)	
IP degree of protection	IP67	
Ambient Air Temperature for Operation	-22158 °F (-3070 °C)	
Ambient Air Temperature for Storage	-40212 °F (-40100 °C)	
Relative humidity	100 % without condensation	
Vibration resistance	+/-1 mm 1055 Hz)IEC 60068-2-6	
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27	
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3	
Resistance to fast transients	1 kV level 3 IEC 61000-4-4	

Ordering and shipping details

Category	22490-SENSORS-ULTRASONIC (XX5,6)	
Discount Schedule	DS2	
GTIN	785901234692	
Nbr. of units in pkg.	1	
Package weight(Lbs)	2.24 oz (63.503 g)	
Returnability	Yes	
Country of origin	US	

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	5.63 in (14.288 cm)	
Package 1 width	2.50 in (6.35 cm)	
Package 1 Length	5.63 in (14.288 cm)	

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months