

REV. 0

DCO 15846

COIL: @ 25°C	
RESISTANCE	768 OHMS ±10%
NOMINAL VOLTAGE	23.0 - 37.0 VDC
MUST OPERATE	16.0 VDC
MUST RELEASE	10.0 VDC MAX 3.2 VDC MIN


ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	30	g's
SHOCK	90	g's	11	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES:

OPERATE TIME	5 MS MAX
RELEASE TIME	4 MS MAX
CONTACT BOUNCE	2.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	5 AMPS 28 VDC
	RESISTIVE 100,000 OPERATIONS MIN

DR. B.D. 9/29/99 CK 9/29/99



CUST.	GENICOM
CUST. NO.	3SBK5152L1 REV.

FW5A RELAY

FW5A11129S02