

H2DBTC-10-13LX+



5-1000MHz

50Ω 10dB Directional Coupler

Features





- Operating temperature range: -40℃ to +85℃
- Storage temperature range: -55℃ to +100℃
- 260℃ Reflow Compatible
- RoHS compliant and lead free
- Input Power:250 mW
- DC Current:30 mA

Applications



- For Motorola Walkie-talkie.
- For Car Streaming Media Rearview Mirror.
- For Broadband and Wireless Communications.
- For Wireless Microphone & Marine Communications.
- For Ideally Suited LTE, Cellular, UMTS, WiFi, WiMAX.
- For Differential Modulator/demodulator and Active Mixers.

Electrical Specifications:TA=25℃, 0dBm, Z0=50Ω


Parameter	Test Conditions	Units	Min	Typ	Max
Coupling(Pin1-3)	5-1000MHz	dB	9.2	10.0	10.8
Main line Loss(Pin1-6)	5-1000MHz	dB	—	1.2	2.0
Input Return Loss(Pin1)	5-1000MHz	dB	16.0	20.0	—
Coupling Return Loss(Pin3)	5-1000MHz	dB	16.0	20.0	—
Output Return Loss(Pin6)	5-1000MHz	dB	18.0	25.0	—
Isolation(Pin3-6)	5-1000MHz	dB	18.0	25.0	—




Outline Drawing(mm)



Electrical structure



Recommended layout(mm)



Pin Connections

Input	1
Coupling	3
Output	6
Ground	2
ISOLATE (DO NOT USE)	4, 5