


COIL: @ +25 °C
 RESISTANCE 600 OHMS
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.4 VDC
 MUST RELEASE 1.5 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX.
RELEASE TIME 3 MS MAX.
CONTACT BOUNCE 3 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 4 AMPS
30 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/11/91 CK. 12/11/91



CUST. Hi-G
 CUST. NO. 2HA-2C-126

TYPE HFW4A RELAY

HFW4A1240S01