


## Product Features

1. Output Frequency : 1 ~ 200MHz
2. Frequency Stability :  $\pm 25$ ,  $\pm 50$  ppm
3. Supply Voltage : 1.8, 2.5, 3.3V
4. Operating Temperature : -40~105°C
5. Output Type : CMOS
6. Phase Jitter : 1ps (Max.) @100MHz, 3.3V
7. RoHS and REACH Compliant, Pb-free, Halogen-free
8. Fast Delivery
9. Industry Standard Package :  
3.2 x 2.5 x 1.0 mm

### Application :

- NB, PC, Tablet, Smartphone, PC peripherals, IPC, Server, Storage, Ethernet, USB, etc.
- Audio ADC, Video, AI Vision Processing Unit, CPLD, FPGA, CPU, GPU, MCU, BMC, etc.



Test condition

Ambient temperature : 25 ± 5°C

Relative humidity : 40% ~ 70%

### ● Table 1 . Electrical Specifications

Parameters	Symbol	Min.	Typ.	Max.	Units	Notes
<b>Frequency Range and Stability</b>						
Nominal Frequency	F	<b>1 ~ 156.25</b>		MHz	@ 2.5 V & 3.3 V	
		<b>1 ~ 125</b>			@ 1.8 V	
Frequency Tolerance	FT	<b>± 25</b>		ppm	@ -40~85°C , Note 1	
		<b>± 50</b>			@ -40~105°C , Note 1	
<b>Operating Temperature Range</b>						
Operating Temperature	Topr	-40	25	105	°C	
<b>Supply Voltage and Current Consumption</b>						
Supply Voltage	Vdd	<b>1.8, 2.5, 3.3 (± 10%)</b>			V	
Current Consumption	Icc	-	-	25	mA	
Standby Current	Icc(ST)	-	-	10	uA	OE = Low
<b>CMOS Type Signal Characteristics</b>						
Output Load : CMOS	CL	<b>15</b>			pF	
Output Voltage High	VoH	<b>90%Vdd</b>	-	-	V	<b>Vdd @ 2.5 or 3.3 V</b>
		<b>Vdd-0.4</b>	-	-		<b>Vdd @ 1.8 V</b>
Output Voltage Low	VoL	-	-	<b>10%Vdd</b>	V	<b>Vdd @ 2.5 or 3.3 V</b>
		-	-	<b>0.4</b>		<b>Vdd @ 1.8 V</b>
Rise Time	Tr	-	-	<b>5</b>	ns	<b>10% → 90% Vdd Level</b>
		-	-	<b>4</b>	ns	<b>20% → 80% Vdd Level</b>
Fall Time	Tf	-	-	<b>5</b>	ns	<b>90% → 10% Vdd Level</b>
		-	-	<b>4</b>	ns	<b>80% → 20% Vdd Level</b>
Symmetry (Duty ratio)	TH/T	<b>45</b>	~	<b>55</b>	%	

Note 1: Inclusive of frequency tolerance at 25°C , variation over temperature, supply voltage variation, aging and vibration.

**● Table 1 . Electrical Specifications (continued)**


Test condition  
Ambient temperature :  $25 \pm 5^\circ\text{C}$   
Relative humidity : 40% ~ 70%

Parameters	Symbol	Min.	Typ.	Max.	Units	Notes
<b>Startup and Resume time</b>						
Start-up Time	T <sub>osc</sub>	-	-	10	ms	To 90% of Final Amplitude
Output Disable Delay Time	T <sub>off</sub>	-	-	250	us	
Output Enable Delay Time	T <sub>on</sub>	-	-	300	us	
<b>Enable Pin Control and Input Characteristics</b>						
Enable Control	-	Yes			-	Pad 1
Enable Voltage High	V <sub>IH</sub>	70%V <sub>dd</sub>	-	-	V	
Disable Voltage Low	V <sub>IL</sub>	-	-	30%V <sub>dd</sub>	V	
<b>Aging Performance</b>						
Aging	-	$\pm 3$		ppm/yr.	1st. Year at $25^\circ\text{C}$	
<b>Jitter Performance</b>						
RMS Phase Jitter Fout range : 10MHz~40MHz @ Integrated from 12KHz ~ 5MHz Note1	PJ	-	-	1.0	ps	
RMS Phase Jitter Fout range : 40MHz~200MHz @ Integrated from 12KHz ~ 20MHz Note1	PJ	-	-	1.0	ps	

Note 1 : Phase Jitter will be slightly different according to output frequency and supply voltage.

**● Test Diagram**


Pad 1(OE)	Pad 3 (Output)	Oscillator
High (or open)	OSC out	Normal operation
Low	High impedance	Stop oscillation



Note : TXC sets CL to 15pF for simulation IC load. Customer does not need to layout it in reality circuit.

## ● Waveform Conditions

Waveform measurement system should have a min. bandwidth of 5 times the frequency being tested.



## ● Dimensions & Footprint (Recommended)

Unit : mm

