



产品规格书

ITEM	XRRH3.5*4.7*0.8 TAPING
PART NO.	
ELECTRICAL REQUIREMENTS	IMPEDANCE Z:48 MIN OHM(100MHZ)

TEST MEHOD

APPEARANCE STANDARD	VISION
INSPECTION LEVEL	MIL-SID-105D AQL=0.1
CHARACT&SIZE	LEVEL S-3
SURFACE	LEVEL II
TEST EQUIPMENT	HP-4191A
TEST FREQUENCY	100MHZ
COIL SPEC	T.C.Φ0.55*63m/m

DIMENSION (UNIT:mm)




$A=3.50 \pm 0.20\text{m/m}$

$C=0.80 \pm 0.20\text{m/m}$


$D=4.70 \pm 0.20\text{m/m}$

TEST DATA


CUSTOMER		QUANTITY							
ITEM	XRRH3.5*4.7*0.8 TAPING	COIL SPEC							
PART NO.		TEST FREQUENCY	100MHZ						
HUMIDITY	63%	TEST EQUIPMENT	HP-4191A						
TEMPERATURE	23°C								
	TESTRESOLUTION		DIMENSION(UNIT:mm)						
	Z MHZ	Z1 10MHZ	Z2 100MHZ	A	B	C	D	E	F
SPEC	Ω MIN	Ω MIN	48 Ω MIN	3.50 ± 0.20		0.80 ± 0.20	4.70 ± 0.20		
1			57	3.51		0.87	4.78		
2			55	3.50		0.85	4.75		
3			58	3.49		0.90	4.80		
4			58	3.50		0.88	4.79		
5			60	3.51		0.89	4.76		
6									
7									
8									
9									
10									
MEAN									
R									



ITEM : L5 XRRH3.5*4.7*0.8 TAPING



METER: HP-4191A



ITEM	XRRH3.5*4.7*0.8 TAPING
PART NO.	

PACKAGING

Available in tape and reel bulk

TAPE DIMENSION:

TYPE	B	E	F	H	I	J	P	d1-d2
XRRH3.5*4.7*0.8	63.00	6.00	52.0	4.20	1.35	0.80	5.00	1.20
	±3.00	±0.50	±1.50	MIN	MAX	MAX	±0.50	MAX

