This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.



### Data Sheet

HD-EM1206-SC-R

PUI Audio's 12.4mm long by 3.8mm wide and high **HD-EM1206-SC-R** is an eccentric rotating mass vibration haptic motor. Originally designed for use in pagers/beepers, this device is great for use in wearables for haptic feedback.

#### **Features:**


- Driven with positive or negative DC for clockwise or counterclockwise movement
- Convenient spring contacts for simple electrical connection
- 12,000 RPMs with 3 VDC input

### **Specifications**

| Parameters                   | Values        | Units |
|------------------------------|---------------|-------|
| Rated Voltage                | 3             | VDC   |
| Operating Voltage Range      | 2.4 ~ 3.6     | VDC   |
| Terminal Resistance          | 30 ±20%       | Ohms  |
| Rated Speed (at 3 VDC)       | 12,000 ±3,000 | RPMs  |
| Current Draw (at 3 VDC)      | 90            | mA    |
| Stall Current Draw           | 120           | mA    |
| Insulation Resistance        | 1             | MOhms |
| Acoustic Noise (Max)         | 50            | dBA   |
| Housing Material             | SPC           | -     |
| Acceptable Soldering Methods | N/A           | -     |
| Environmental Compliances    | RoHS/REACH    | -     |
| Weight                       | 1             | Grams |
| Storage Temperature          | -40 ~ +85     | °C    |
| Operating Temperature        | -20 ~ +60     | °C    |


This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.

## **Measurement Methods**



- Specification of the dummy Jig
  - Size : 45mm x 105mm x 15mm
  - · Weight : 100gr
  - · Material : Bakelite
  - · Vibration motor should be attached by using a double-sided tape

## Acoustic noise




### **Reliability Testing**

| Type of Test                  | Test Specifications   |
|-------------------------------|---|
| High Temperature Test         | 96 hours at 85°C  |
| Low Temperature Test          | 96 hours at -40°C   |
| H2S Corrosion Resistance Test | Concentration: 3 ±1 PPM<br>Test Environment: 40°C, humidity 80% RH<br>Test Duration Time: 240 hours             |
|                               | Temperature: -20°C to +60°C   |
|                               | Test Duration: 30 minutes   |
| Temperature Cycle Testing     | Test Cycles: 15 cycles  |
| Vibration Test                | 3mm deflection at 1000 cycles per minute, for 10 minutes in each axis (X, Y, Z).                                |
|                               | Weight: Set the linear vibration motor to the around 100g (include the linear vibration motor) weight of block. |
|                               | Drop Height: 150cm  |
|                               | Floor Material: Steel   |
|                               | Direction: $\pm X$ , $\pm Y$ , $\pm Z$ ; total 6 faces  |
| Drop Test                     | Number of Times: Each face 3 Times  |
|                               | 60,000 operating cycles in room temperature   |
| Load Test                     | Cycle test condition: 2 seconds on, 2 second off  |

Acceleration, resistance, rated current and noise must meet specifications after allowing the device to rest for 4 hours after test.

# Dimensions (Left contact is positive when looking from the rear of the part. See far left image below.)



## This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.

| Specifications Revisions |                           |          |  |
|--------------------------|---------------------------|----------|--|
| Revision                 | Description               | Date     |  |
| А                        | Released from Engineering | 4/6/2021 |  |

Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- 2. Specifications subject to change or withdrawal without notice.