



Dual Phase Leg SiC MOSFET Power Module

Product Overview

The MSCSM120HM16CTBL3NG device is a dual phase leg 1200 V/150 A silicon carbide (SiC) MOSFET power module.



All ratings at $T_J = 25^\circ\text{C}$, unless otherwise specified.

Caution: These devices are sensitive to electrostatic discharge. Proper handling procedures must be followed.

Features

The following are the key features of MSCSM120HM16CTBL3NG device:

- SiC Power MOSFET
 - Low $R_{DS(on)}$
 - High speed switching
- SiC Schottky Diode
 - Zero reverse recovery
 - Zero forward recovery
 - Temperature independent switching behavior
 - Positive temperature coefficient on V_F
- Very low stray inductance
- Ultra-low weight and profile
- Kelvin source for easy drive
- Si3N4 substrate with thick copper for improved thermal performance
- Internal thermistor for temperature monitoring
- Extended temperature range

Benefits

The following are the benefits of MSCSM120HM16CTBL3NG device:

- High efficiency converter
- Outstanding performance at high frequency operation
- Direct mounting to heatsink (isolated package)
- Low junction-to-case thermal resistance
- Low profile
- RoHS compliant
- Solderable terminals both for power and signal for easy PCB mounting
- Very integrated power conversion system

Application

The following are the applications of MSCSM120HM16CTBL3NG device:

- High reliability power systems
- High Efficiency AC/DC and DC/AC converters
- Motor control

1. Electrical Specifications

This section provides the electrical specifications of MSCSM120HM16CTBL3NG device.

1.1 SiC MOSFET Characteristics (Per SiC MOSFET)

The following table lists the absolute maximum ratings of MSCSM120HM16CTBL3NG device.

Table 1-1. Absolute Maximum Ratings

Symbol	Parameter	Maximum Ratings	Unit
V_{DSS}	Drain-Source voltage	1200	V
I_D	Continuous drain current	$T_H = 25^\circ\text{C}$	150
		$T_H = 80^\circ\text{C}$	120
I_{DM}	Pulsed drain current	300	
V_{GS}	Gate-Source voltage	-10/25	V
$R_{DS(on)}$	Drain-Source ON resistance	16	$\text{m}\Omega$
P_D	Power dissipation	$T_H = 25^\circ\text{C}$	560

The following table lists the electrical characteristics of MSCSM120HM16CTBL3NG device.

Table 1-2. Electrical Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
I_{DSS}	Zero gate voltage drain current	$V_{GS} = 0 \text{ V}; V_{DS} = 1200 \text{ V}$	—	20	200	μA
$R_{DS(on)}$	Drain-Source on resistance	$V_{GS} = 20 \text{ V}$	$T_J = 25^\circ\text{C}$	12.5	16	$\text{m}\Omega$
		$I_D = 80 \text{ A}$	$T_J = 175^\circ\text{C}$	20	—	
$V_{GS(th)}$	Gate threshold voltage	$V_{GS} = V_{DS}; I_D = 2 \text{ mA}$	1.8	2.8	—	V
I_{GSS}	Gate-Source leakage current	$V_{GS} = 20 \text{ V}; V_{DS} = 0 \text{ V}$	—	—	200	nA

MSCSM120HM16CTBL3NG

Electrical Specifications

The following table lists the dynamic characteristics of MSCSM120HM16CTBL3NG device.

Table 1-3. Dynamic Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
C_{iss}	Input capacitance	$V_{GS} = 0 \text{ V}$ $V_{DS} = 1000 \text{ V}$ $f = 1 \text{ MHz}$	—	6040	—	pF
C_{oss}	Output capacitance		—	540	—	
C_{rss}	Reverse transfer capacitance		—	50	—	
Q_g	Total gate charge	$V_{GS} = -5 \text{ V}/20 \text{ V}$ $V_{Bus} = 800 \text{ V}$ $I_D = 80 \text{ A}$	—	464	—	nC
Q_{gs}	Gate-Source charge		—	82	—	
Q_{gd}	Gate-Drain charge		—	100	—	
$T_{d(on)}$	Turn-on delay time	$V_{GS} = -5 \text{ V}/20 \text{ V}$ $V_{Bus} = 600 \text{ V}$ $I_D = 100 \text{ A}$	—	30	—	ns
T_r	Rise time		—	30	—	
$T_{d(off)}$	Turn-off delay time		—	50	—	
T_f	Fall time	$R_{Gon} = 4 \Omega$; $R_{Goff} = 2.4 \Omega$			25	—
E_{on}	Turn-on energy		$T_J = 150 \text{ }^\circ\text{C}$	—	1.98	—
E_{off}	Turn-off energy		$T_J = 150 \text{ }^\circ\text{C}$	—	1.3	—
R_{Gint}	Internal gate resistance			—	1.94	—
R_{thJH}	Junction-to-heatsink thermal resistance	$\lambda = 3.4 \text{ W/mK}$		—	0.268	—
						°C/W

The following table lists the body diode ratings and characteristics of MSCSM120HM16CTBL3NG device.

Table 1-4. Body Diode Ratings and Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
V_{SD}	Diode forward voltage	$V_{GS} = 0 \text{ V}; I_{SD} = 80 \text{ A}$	—	4	—	V
		$V_{GS} = -5 \text{ V}; I_{SD} = 80 \text{ A}$	—	4.2	—	
t_{rr}	Reverse recovery time	$I_{SD} = 80 \text{ A}; V_{GS} = -5 \text{ V}$ $V_R = 800 \text{ V}; dI/dt = 2000 \text{ A}/\mu\text{s}$	—	90	—	ns
Q_{rr}	Reverse recovery charge		—	1100	—	
I_{rr}	Reverse recovery current		—	27	—	

1.2**SiC Diode Ratings and Characteristics (Per SiC Diode)**

The following table lists the SiC diode ratings and characteristics of MSCSM120HM16CTBL3NG device.

Table 1-5. SiC Diode Ratings and Characteristics (Per SiC Diode)

Symbol	Characteristic	Test Conditions		Min	Typ	Max	Unit
V_{RRM}	Peak repetitive reverse voltage				—	—	1200 V
I_{RRM}	Reverse leakage current	$V_R = 1200 \text{ V}$	$T_J = 25 \text{ }^\circ\text{C}$	—	20	400	μA
			$T_J = 175 \text{ }^\circ\text{C}$	—	300	—	
I_F	DC forward current		$T_H = 100 \text{ }^\circ\text{C}$	—	60	—	A
V_F	Diode forward voltage	$I_F = 60 \text{ A}$	$T_J = 25 \text{ }^\circ\text{C}$	—	1.5	1.8	V
			$T_J = 175 \text{ }^\circ\text{C}$	—	2.1	—	
Q_C	Total capacitive charge	$V_R = 600 \text{ V}$		—	260	—	nC
C	Total capacitance	$f = 1 \text{ MHz}, V_R = 400 \text{ V}$		—	282	—	pF
		$f = 1 \text{ MHz}, V_R = 800 \text{ V}$		—	210	—	
R_{thJH}	Junction-to-heatsink thermal resistance	$\lambda_{\text{paste}} = 3.4 \text{ W/mK}$	—	0.45	—	—	°C/W

1.3**Thermal and Package Characteristics**

The following table lists the thermal and package characteristics of MSCSM120HM16CTBL3NG device.

Table 1-6. Thermal and Package Characteristics

Symbol	Characteristic	Min	Typ	Max	Unit	
V_{ISOL}	RMS isolation voltage, any terminal to case t = 1 min, 50 Hz/60 Hz	2500	—	—	V	
T_J	Operating junction temperature range	-55	—	175	°C	
T_{JOP}	Recommended junction temperature under switching conditions	-55	—	$T_{J\max}-25$		
T_{STG}	Storage case temperature	-55	—	125		
T_C	Operating case temperature	-55	—	125		
Torque	Mounting torque	To heatsink	M3	0.7	—	0.9 N.m
Wt	Package weight	—	32.5	—	g	

The following table lists the temperature sensor NTC of the MSCSM120HM16CTBL3NG device.

Table 1-7. Temperature Sensor NTC

Symbol	Characteristic		Min	Typ	Max	Unit
R ₂₅	Resistance at 25°C	—	—	50	—	kΩ
ΔR ₂₅ /R ₂₅	—	—	—	5	—	%
B _{25/85}	T ₂₅ = 298.15 K	—	—	3952	—	K
ΔB/B	—	T _C = 100°C	—	4	—	%

$$R_T = \frac{R_{25}}{\exp\left[B_{25/85}\left(\frac{1}{T_{25}} - \frac{1}{T}\right)\right]} \quad T: \text{Thermistor temperature}$$

R_T: Thermistor value at T

Note: See APT0406—Using NTC Temperature Sensor Integrated into Power Module for more information.

1.4

Typical SiC MOSFET Performance Curve

This section shows the typical SiC MOSFET performance curves of the MSCSM120HM16CTBL3NG device.

Figure 1-1. Junction-to-Heatsink Thermal Impedance




Figure 1-2. Output Characteristics, T_J = 25 °C




Figure 1-3. Output Characteristics, T_J = 175 °C










Figure 1-4. Normalized $R_{DS(on)}$ vs. Temperature**Figure 1-5. Transfer Characteristics****Figure 1-6. Switching Energy vs. R_g** **Figure 1-7. Switching Energy vs. Current****Figure 1-8. Capacitance vs. Drain Source Voltage****Figure 1-9. Gate Charge vs. Gate Source Voltage**









Figure 1-10. Body Diode Characteristics, $T_J = 25^\circ\text{C}$ Figure 1-11. 3rd Quadrant Characteristics, $T_J = 25^\circ\text{C}$ Figure 1-12. Body Diode Characteristics, $T_J = 175^\circ\text{C}$ Figure 1-13. 3rd Quadrant Characteristics, $T_J = 175^\circ\text{C}$ 

Figure 1-14. Operating Frequency vs Drain Current



1.5**Typical SiC Diode Performance Curves**

This section shows the typical SiC diode performance curves of the MSCSM120HM16CTBL3NG device.

Figure 1-15. Junction-to-Heatsink Thermal Impedance**Figure 1-16. Forward Characteristics****Figure 1-17. Capacitance vs. Reverse Voltage**


2. Package Specifications

The following section shows the package specification of MSCSM120HM16CTBL3NG device.

2.1 Package Outline

The following figure shows the package outline drawing of MSCSM120HM16CTBL3NG device. The dimensions in the following figure are in millimeters.

Figure 2-1. Package Outline Drawing



3. Revision History

Revision	Date	Description
A	07/2021	Initial revision

The Microchip Website

Microchip provides online support via our website at www.microchip.com/. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** – Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** – Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- **Business of Microchip** – Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Product Change Notification Service

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to www.microchip.com/pcn and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Embedded Solutions Engineer (ESE)
- Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: www.microchip.com/support

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Legal Notice

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBloX, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQi, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBloX, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2021, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-8533-9

Quality Management System

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



MICROCHIP

Worldwide Sales and Service

AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: www.microchip.com/support Web Address: www.microchip.com Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455 Austin, TX Tel: 512-257-3370 Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088 Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075 Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924 Detroit Novi, MI Tel: 248-848-4000 Houston, TX Tel: 281-894-5983 Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380 Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800 Raleigh, NC Tel: 919-844-7510 New York, NY Tel: 631-435-6000 San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270 Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078	Australia - Sydney Tel: 61-2-9868-6733 China - Beijing Tel: 86-10-8569-7000 China - Chengdu Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588 China - Dongguan Tel: 86-769-8702-9880 China - Guangzhou Tel: 86-20-8755-8029 China - Hangzhou Tel: 86-571-8792-8115 China - Hong Kong SAR Tel: 852-2943-5100 China - Nanjing Tel: 86-25-8473-2460 China - Qingdao Tel: 86-532-8502-7355 China - Shanghai Tel: 86-21-3326-8000 China - Shenyang Tel: 86-24-2334-2829 China - Shenzhen Tel: 86-755-8864-2200 China - Suzhou Tel: 86-186-6233-1526 China - Wuhan Tel: 86-27-5980-5300 China - Xian Tel: 86-29-8833-7252 China - Xiamen Tel: 86-592-2388138 China - Zhuhai Tel: 86-756-3210040	India - Bangalore Tel: 91-80-3090-4444 India - New Delhi Tel: 91-11-4160-8631 India - Pune Tel: 91-20-4121-0141 Japan - Osaka Tel: 81-6-6152-7160 Japan - Tokyo Tel: 81-3-6880- 3770 Korea - Daegu Tel: 82-53-744-4301 Korea - Seoul Tel: 82-2-554-7200 Malaysia - Kuala Lumpur Tel: 60-3-7651-7906 Malaysia - Penang Tel: 60-4-227-8870 Philippines - Manila Tel: 63-2-634-9065 Singapore Tel: 65-6334-8870 Taiwan - Hsin Chu Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830 Taiwan - Taipei Tel: 886-2-2508-8600 Thailand - Bangkok Tel: 66-2-694-1351 Vietnam - Ho Chi Minh Tel: 84-28-5448-2100	Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829 Finland - Espoo Tel: 358-9-4520-820 France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79 Germany - Garching Tel: 49-8931-9700 Germany - Haan Tel: 49-2129-3766400 Germany - Heilbronn Tel: 49-7131-72400 Germany - Karlsruhe Tel: 49-721-625370 Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44 Germany - Rosenheim Tel: 49-8031-354-560 Israel - Ra'anana Tel: 972-9-744-7705 Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781 Italy - Padova Tel: 39-049-7625286 Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340 Norway - Trondheim Tel: 47-72884388 Poland - Warsaw Tel: 48-22-3325737 Romania - Bucharest Tel: 40-21-407-87-50 Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 Sweden - Gothenberg Tel: 46-31-704-60-40 Sweden - Stockholm Tel: 46-8-5090-4654 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820