

Power Transformer Chassis Mount: Quick Pack

F4-36

Description:

The F4-36 Quick Pack small power transformer offers a significant reduction in size and weight over a standard transformer. This transformer can be used for a wide variety of applications. It is bobbin wound for reduced size and small operating space.

Electrical Specifications (@25C);

Maximum Power: 6.0VA

Input Voltage: 115VAC@50/60Hz Output Voltage: 36VCT@0.17A¹

Recommended Fuse: UL listed 250VAC, 0.2A, Slo-Blo

Hipot: 2500VAC primary to secondary; 1500VAC windings to core.

Construction:

Split bobbin non concentric winding eliminates costly electrostatic shielding. Termination is suitable for quick connects or soldering. Built with UL Class B Insulation System.

Safetv:

UL: File E53148, UL 5085-1 and 2 (formerly UL 506), General Purpose.

UL: File E65390, UL5085-1 and 3, Class 3



Dimensions:


| А | В | С | D | Е | F | G |
|-------|---------|-------|-------|-------|----------|------|
| 1.375 | 2.0±.03 | 2.375 | 1.250 | 1.687 | .187 Dia | .687 |

Notes: 1. Units: inches.

2. Terminal size: .187" X 0.021".

3. Weight: .44 lbs

Schematic:




Input: Input 2 & 3
Output: 5 to 8


RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.


* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

Web: www.TriadMagnetics.com Phone 951-277-0757 Fax 951-277-2757

460 Harley Knox Blvd. Perris, California 92571







¹ Fuse must be used on **secondary** as conditions of acceptability for UL Class 2/3 operation.