


TO-220 Plastic-Encapsulate Voltage Regulators

DESCRIPTION


This monolithic integrated circuit is an adjustable 3-terminal positive voltage regulator designed to supply more than 1.5A of load current with an output voltage adjustable over a 1.2 to 37V. It employs internal current limiting, thermal shut-down and safe area compensation.

FEATURE

- Internal thermal overload protection
- Internal short circuit current limiting
- Output transistor safe operating area compensation



Internal Block Diagram



Absolute Maximum Ratings

Symbol	Parameter	Value	Unit
$V_I - V_O$	Input-Output Voltage Differential	40	V
T_{LEAD}	Lead Temperature	230	°C
P_D	Power Dissipation	Internally limited	W
T_J	Operating Junction Temperature Range	-20~125	°C
T_{stg}	Storage Temperature Range	-55~125	
$\Delta V_O / \Delta T$	Temperature Coefficient of Output Voltage	±0.02	%/°C


ELECTRICAL CHARACTERISTICS(V_O-V_I=5V, I_O=0.5A, 0°C≤T_J≤+125°C, I_{MAX}=1.5A, P_{DMAX}=20W, unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Line Regulation(note1)	R_{line}	$T_A=25^\circ C$ 3V≤V _I -V _O ≤40V		0.01	0.04	%/V
		3V≤V _I -V _O ≤40V		0.02	0.07	
Load Regulation(note1)	R_{load}	$T_A=25^\circ C$, 10mA≤I _O ≤I _{MAX} V _O <5V V _O ≥5V		18 0.4	25 0.5	mV%/ V _O
		10mA≤I _O ≤I _{MAX} V _O <5V V _O ≥5V		40 0.8	70 1.5	
Adjustable Pin Current	I _{ADJ}	-		46	100	μA
Adjustable Pin Current Change	ΔI _{ADJ}	3V≤V _I -V _O ≤40V 10mA≤I _O ≤I _{MAX} , P _D ≤P _{MAX}		2.0	5	
Reference Voltage	V _{REF}	3V≤V _{IN} -V _O ≤40V 10mA≤I _O ≤I _{MAX} , P _D ≤P _{MAX}	1.20	1.25	1.30	V
Temperature Stability	S _T	-		0.7		%/ V _O
Minimum Load Current to Maintain Regulation	I _{L(MIN)}	V _I -V _O =40V		3.5	12	mA
Maximum Output Current	I _{O(MAX)}	V _I -V _O ≤15V, P _D ≤P _{MAX} V _I -V _O ≤40V, P _D ≤P _{MAX} $T_A=25^\circ C$	1.0	0.3	2.2	A
RMS Noise,% of V _{OUT}	e _N	$T_A=25^\circ C$, 10Hz≤f≤10KHz		0.003	0.01	%/ V _O
Ripple Rejection	RR	V _O =10V, f =120Hz without C _{ADJ} C _{ADJ} =10μF(note2)	66	60 75		dB
Long-Term Stability,T _J =T _{HIGH}	ST	$T_A=25^\circ C$ for end point measurements,1000HR		0.3	1	%
Thermal Resistance Junction to case	R _{θJC}	-		5		°C/W

Notes:

1. Load and line regulation are specified at constant junction temperature. Change in V_D due to heating effects must be taken into account separately. Pulse testing with low duty is used.(P_{MAX}=20W)
- 2.C_{ADJ}. when used, is connected between the adjustment pin and ground.

Typical Application



$$V_o = 1.25V \left(1 + \frac{R_2}{R_1}\right) + I_{adj}R_2$$

C_i is required when regulator is located an appreciable distance from power supply filter.

C_o is not needed for stability, however, it does improve transient response.

Since I_{ADJ} is controlled to less than 100 μA, the error associated with this term is negligible in most applications.