



A Product Line of Diodes Incorporated

SEMICONDUCTOR

LITE-ON

TT10M(LS)

Product Summary

VRRM (V)	IF (A)	V _F Max (V) @ I _F = 5A	I _R Max (μA)
1000	10	1.05	5

Mechanical Data

- Package: TTL
- Package Material: "Green" Molding Compound, UL Flammability Classification 94V-0 (No Br. Sb. Cl.)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (2)
- Polarity Indicator: As Marked on the Body
- Weight: 0.41 grams (Approximate)

10A STANDARD RECOVERY BRIDGE RECTIFIER

Features

- Glass Passivated Die Construction
- Ideal for Printed Circuit Board
- Reliable Low Cost Construction Utilizing Molded Plastic
 Technique
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>





Ordering Information (Note 4)

Part Number	Packaga	Packing	
	Package	Qty.	Carrier
TT10M_HF	TTL	1500	Reel


EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and

Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

Notes:



TT10M = Product Type Marking Code YMWW = Date Code Marking Y = Year Code (ex: 2 = 2022) M = Manufacturer's Internal Code WW = Week Code (01 to 53)





TT10M(LS)

Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic			Value	Unit
Maximum Repetitive Peak Reverse Voltage		Vrrm	1000	V
Maximum DC Blocking Voltage		V _{DC}	1000	V
Average Rectified Output Current	@T _A = +25°C (Note 5)	lf(AV)	10	А
Peak Forward Surge Current 8.3ms Single Half Sine-Wave	@T _A = +25°C @T _A = +125°C	I _{FSM}	180 144	А
Peak Forward Surge Current 1.0ms Single Half Sine-Wave	@T _A = +25°C @T _A = +125°C	I _{FSM}	360 288	А
I ² t Rating for Fusing (t = 8.3ms)		l ² t	135	A ² s
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Test Condition		Symbol	Тур.	Max	Unit
Forward Voltage (Note 5)		T _A = +25°C	VF	0.98	1.05	- V
	IF = 5A	T _A = +125°C	VF	0.88	—	
Leakage Current	V _R = 1000V	$T_A = +25^{\circ}C$	I-	0.2	5	μA
		T _A = +125°C	IR	70	500	
Typical Junction Capacitance (Note 6)			Ст	5	0	pF

Thermal Characteristics

Notes:

Characteristic	Symbol	Тур.	Unit
Typical Thermal Resistance (Without Heatsink)	Rejc Rejl Reja	11 13 72	°C/W
Typical Thermal Resistance (Note 7)	Rejc Rejl Reja	2 5 10	°C/W


5. Perform static test after the temperature of oven is steady for 20 minutes.
 6. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
 7. Thermal resistance junction to case, lead and ambient in accordance with JESD-51.



A Product Line of Diodes Incorporated

LITE-ON SEMICONDUCTOR

TT10M(LS)






LITE-ON SEMICONDUCTOR

TT10M(LS)

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




	TTL					
Dim	Min	Max	TYP			
Α	1.45	1.80	1.65			
A1	0.00	0.15	0.10			
A2	1.45	1.65	1.55			
b	1.30	1.50	1.40			
С	0.15	0.35	0.25			
D	10.05	10.35	10.20			
ш	9.75	10.05	9.90			
E1	6.85	7.15	7.00			
Е	4.90	5.10	5.00			
L	0.45	0.95	0.70			
All C	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

TTL



Dimensions	Value (in mm)	
С	5.00	
Х	1.80	
Y	2.10	
Y1	11.70	



LITE-ON SEMICONDUCTOR

TT10M(LS)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products provided subject to Diodes' Standard Terms and Conditions of Sale 5 are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com