## **SMT Power Inductor**

High Current Composite Inductor - PA/PM5430 and PA/PM5431.XXXNLT

















- Meight: 4.1mm Max
- Footprint: 4.35mm x 4.35mm Max
- © Current Rating: up to 6.6Apk
- Inductance Range: 3.3uH to 15uH
- Rated Voltage between Terminals: 50V
- High current, low DCR, and high efficiency
- Minimized acoustic noise and minimized leakage flux noise

@ Available in Commercial (PA543X) and Automotive (PM543X) grades(PM5430) grades

Electrical Specifications @ 25°C, Operating Temperature Range -55°C to +155°C									
Part Number		©Inductance 100KHz, 0.1V	Rated³ Current	DC Resistance	lsat²	SRF	K Factor for		
Commerical	Automotive <sup>6</sup>	uH±20%	A	mΩ MAX.	A MAX	MHz	Core Loss		
PA5430.332NLT	PM5430.332NLT	3.3	6.6	28.6	5.5	43	133		
PA5430.472NLT	PM5430.472NLT	4.7	5.1	44.1	4.5	36	101		
PA5430.682NLT	PM5430.682NLT	6.8	3.9	74.1	3.6	29	90		
PA5431.822NLT	PM5431.822NLT	8.2	3.4	66.9	3.4	15	74		
PA5431.103NLT	PM5431.103NLT	10	3.1	92.4	2.5	13	71		
PA5431.153NLT	PM5431.153NLT	15	2.8	120	2.3	11	51		

#### Notes:

- Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- The saturation current is the current at which the initial inductance is guaranteed to drop by no more than 40%.
- The rated current is the DC current required to raise the component temperature by approximately 40°C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- The part temperature (ambient+temp rise) should not exceed 155°C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be

- verified in the end application.
- Parts shown in bold are standard catalog parts and are available through sample stock and distribution. Parts in lighter font are available but are not necessarily held in sample stock or distribution and lead times may be longer. Please contact Pulse for availablity.
- The PM543X.XXXNLT series are AEC-Q200 certified and IATF 16949 compliance, but the resistance to solvents test is waived. The inductance and mechanical dimensions will do 100% test in mass production due to the Cpk <1.33.
- Special Characteristics of for PM543X.XXXNLT.

PulseElectronics.com P900.D (09/23)


# **SMT** Power Inductor


High Current Composite Inductor - PA/PM5430 and PA/PM5431.XXXNLT



#### Mechanical

#### PA5430/PM5430.XXXNLT and PA5431.XXXNLT






ı	FI	N	Δ	Ш	LA	γ	N	H.	T


SUGGESTED PAD LAYOUT

Series	А	В	C	D	Е	F	L	G	Н
PA5430/PM5430	4.1±0.25	4.1±0.25	2.8±0.3	3.4±0.3	0.88±0.3	1.6±0.3	3.4 (REF)	1.4 (REF)	3.8 (REF)
PA5431/PM5431	4.1±0.25	4.1±0.25	3.8±0.3	3.4±0.3	0.88±0.3	1.6±0.3	3.4 (REF)	1.4 (REF)	3.8 (REF)

All Dimensions in mm.

#### **TAPE & REEL INFO**





Direction of tape

SURFACE MOUNTING TYPE, REEL/TAPE LIST									
Carias	REEL SIZE (mm)		TA	QTY					
Series	A	G	P <sub>1</sub>	W	$K_{_{0}}$	PCS/REEL			
PA5430/PM5430	Ø330	12.4	8	12	3.3	2000			
PA5431/PM5431	Ø330	12.4	8	12	4.5	1800			

2 PulseElectronics.com P900.D (09/23)




**CORE LOSS vs FLUX DENSITY** 

3

#### **CORE LOSS vs FLUX DENSITY**

PA/PM5430.XXXNLT




Bp-pK\*L(uH)\*Delta I(A)

PulseElectronics.com P900.D (09/23)

### **CORE LOSS vs FLUX DENSITY**

PA/PM5430.XXXNLT



Bp-pK\*L(uH)\*Delta I(A)

Americas - prodinfo\_power\_americas@yageo.com | Europe - prodinfo\_power\_emea@yageo.com | Asia - prodinfo\_power\_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

