

December 1993

**3A, 50V - 600V Diodes**

**Features**

- Glass Passivated Junction
- Fast Recovery Times
- Low Forward Voltage Drop, High-Current Capability
- Low Reverse Current Leakage
- High Surge Current Capability


**Description**

The Harris A115A, A115B, A115C, A115D, A115E, A115F, and A115M are fast-recovery silicon rectifiers ( $t_{RR} = 250\text{ns}$  max.) featuring low forward voltage drop, high-current capability. They use glass passivated epitaxial construction.

These rectifiers are intended for TV deflection, inverter, high-frequency power supplies, energy recovery, and output rectification.

These types are supplied in unitized-glass hermetically-sealed AL-3 package.

**Package**



**Symbol**



**Absolute Maximum Ratings** For Single Phase, 60Hz, Half-Wave Resistive or Inductive Loads (Note 1)

	A115F	A115A	A115B	A115C	A115D	A115E	A115M	UNITS
Maximum Peak (Repetitive)								
Reverse Voltage ..... $V_{RRM}$	50	100	200	300	400	500	600	V
Maximum RMS Input (Supply) Voltage ..... $V_{RMS}$	35	70	140	210	280	350	420	V
Maximum DC Reverse (Blocking) Voltage ..... $V_{R(DC)}$	50	100	200	300	400	500	600	V
Maximum Average Forward Output Current Lead Length = 0.375in. (9.5mm); $T_A = -55^\circ\text{C}$ ..... $I_O$	3	3	3	3	3	3	3	A
Maximum Peak Surge (Non-Repetitive) Forward Current:								
For 8.3ms Half Sine Wave, Superimposed on Rated Load ..... $I_{FSM}$	100	100	100	100	100	100	100	A
Operating Junction and Storage Temperature ..... $T_J, T_{STG}$				-65 to +175				$^\circ\text{C}$

NOTE:

1. For capacitive load derate current by 20%.

**4**  
GENERAL PURPOSE DIODES

## Specifications A115 Series

### Electrical Specifications $T_A = +25^\circ\text{C}$ , Unless Otherwise Specified

PARAMETERS	SYMBOL	LIMITS FOR ALL TYPES			UNITS
		MIN	TYP	MAX	
Maximum Instantaneous Forward-Voltage Drop At 3A	$V_F$	-	-	1.3	V
Maximum Full-Load Reverse Current					
At Average Full-Cycle, Lead Length = 0.375 in. (9.5mm) $T_A = +25^\circ\text{C}$	$I_R$	-	-	2	$\mu\text{A}$
At Average Full-Cycle, Lead Length = 0.375 in. (9.5mm) $T_A = +150^\circ\text{C}$	$I_R$	-	-	100	$\mu\text{A}$
Maximum DC Reverse Current at Maximum DC Blocking Voltage	$I_R$	-	-	5	$\mu\text{A}$
Maximum Reverse Recovery Time					
At $I_F = 0.5\text{A}$ , $I_R = 1\text{A}$ , $I_{RR} = 0.25\text{A}$	$t_{RR}$	-	-	150 (Note 1)	$\mu\text{s}$
Typical Junction Capacitance At Frequency = 1MHz and Applied Reverse Voltage = 4V	$C_J$	-	40	-	pF

NOTE:

- 250ns for A115M

### Typical Performance Curves




FIGURE 1. MAXIMUM AVERAGE FORWARD OUTPUT CURRENT CHARACTERISTIC




FIGURE 2. MAXIMUM PEAK SURGE (NON-REPETITIVE) FORWARD CURRENT CHARACTERISTIC

Typical Performance Curves (Continued)




FIGURE 3. TYPICAL INSTANTANEOUS FORWARD CURRENT CHARACTERISTIC




FIGURE 4. TYPICAL REVERSE LEAKAGE CURRENT CHARACTERISTICS




FIGURE 5. TYPICAL JUNCTION CAPACITANCE CHARACTERISTIC





FIGURE 6. REVERSE-RECOVERY TIME WAVEFORM



- NOTES:
1. RISE TIME = 7ns MAX., INPUT IMPEDANCE = 1MΩ, 22pF
  2. RISE TIME = 10ns MAX., SOURCE IMPEDANCE = 50Ω

FIGURE 7. REVERSE-RECOVERY TIME TEST CIRCUIT

4  
GENERAL PURPOSE DIODES