



DEUTSCH

TE Internal #: 6162-213-1677

Coax, Socket Contact, 1 Position, Wire & Cable, Straight, Gold,
Contact Mating Retention, 13 A, Signal[View on TE.com >](#)

Connectors > Contacts > RF Contacts

Contact Type: **Socket**RF Contact Style: **Coax**Number of Positions: **1**Connector & Contact Terminates To: **Wire & Cable**Contact Orientation: **Straight****Features****Product Type Features**

| | |
|-----------------------------------|--------------|
| RF Contact Style | Coax |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 1 |
|---------------------|---|

Contact Features

| | |
|--------------------------------------|----------|
| Contact Underplating Material | Nickel |
| Contact Type | Socket |
| Contact Orientation | Straight |
| Contact Mating Area Plating Material | Gold |
| Contact Mating Retention | With |
| Contact Current Rating (Max) | 13 A |

Operation/Application

| | |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 1 |
| Packaging Method | Bag |

Product Compliance[For compliance documentation, visit the product page on TE.com>](#)









| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |


| | |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

| | | | |
|---|---|---|--|
|  <p>TE Part #1823500-1 COVER,90</p> |  <p>TE Part #2362767-5 MATENET,CABLE ASSY,1 GBPS UTP</p> |  <p>TE Part #929972-1 BU-KONTAKT 2,5MMD</p> |  <p>TE Part #1-964294-3 TAB A 2.8x0.8 CONTACT CS SRC Au</p> |
|  <p>TE Part #3-1617073-3 3SBC2087A2 = M39016/37-017P</p> |  <p>TE Part #EM7079-000 THA-PDKG-05</p> |  <p>TE Part #1-2362764-0 MATENET,CABLE ASSY,1 GBPS UTP</p> |  <p>TE Part #2317303-1 2x3 PORT MATenet FRAME, CODE A</p> |



Documents

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English