This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.



Data Sheet

HD-EMB1806-LW32-R

Features:


- Designed to be driven with a 1.5V DC signal
- Convenient 30mm lead wires and flange mount for easy implementation
- Generates 9,000 rpm with less than 55dB mechanical noise

Specifications

Parameters	Values	Units
Input Voltage (DC)	1.5	V _{DC}
Starting Voltage (DC)	0.8	V _{DC}
Operating Voltage Range (DC)	$1.0 \sim 1.6$	V _{DC}
Direction of Rotation	CW/CCW	-
Rated Speed	9,000 ± 2,500	RPM
Rated Current (Max at $3.0 V_{DC}$)	240	mA
Starting Current (Max at $2.4 V_{DC}$)	420	mA
Terminal Resistance	$4.0 \pm 20\%$	Ohms
Shaft Pull Strength (Min)	3	Kg
Shaft End Play (Max)	0.3	mm
Mechanical Noise (Max)	55	dBA
Environmental Compliances	RoHS/REACH	-
Weight	(approx.) 1	Grams
Storage Temperature	-40 ~ +80	°C
Operating Temperature	-30 ~ +70	°C

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.

Measurement Methods




Reliability Testing

Type of Test	Test Specifications		
	Temperature: +80±2°C		
High Temperature Test	Test Duration Time: 96 hours		
	Temperature: -40±2°C		
Low Temperature Test	Test Duration Time: 96 hours		
	Temperature: 40°C		
	Relative Humidity: 90%		
Humidity Test	Test Duration Time: 96 hours		
	Temperature Cycle: -20 to +70°C		
	Cycle Time: 1 hour		
Thermal Shock Test	Test Repetition: 15 cycles (15 hours total)		
	Drive motor for 0.5 seconds on, 0.5 seconds off at rated		
	voltage		
	Repeat cycle shown 2 times (8 hours total)		
Temperature Cycle Testing	1 cycle 60 c -60 c -90 c -20 c 0 1hr 2 hr 3 hr		
	Vibration: 3mm, 1000cpm		
Vibration Test	Test Axis: XYZ		
	Test Repetition: 10 minutes per axis (30 minutes total)		
Drop Test	Drop Condition: 1m onto iron plate at weight 100g		
Drop Test	Test Repetition: 3 times per side (18 total)		
Load Test	50,000 operating cycles at room temperature Test Cycle: 0.5 seconds on, 0.5 seconds off		

Rated current, speed, starting voltage, and mechanical noise must meet specifications after allowing the device to rest for 12 hours after test.

Dimensions



Packaging

ltem	Tray	Inner Box	Outer Box	
DIV.	PET	Carton box Carton box		
Dimension	141(L) × 150(W) × 11(H)	150(L) × 160(W) × 115(H)	W) × 115(H) 330(L) × 330(W) × 270(H)	
Quantity	50ea	500ea	4,000ea	

Specifications Revisions				
Revision	Description	Date		
А	RELEASED FROM ENGINEERING	04/08/2022		

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.ssw
- 2. Specifications subject to change or withdrawal without notice.