

D±0.10  
02P~10P


P/N LEGEND

A1253 HA-XP		
①	②	③
① Series No.	② Connector type: H=Housing	③ No. of circuits


SPECIFICATIONS

Current Rating: 1A AC,DC  
Voltage Rating: 150V AC,DC  
Temperature Range: -25°C ~ +85°C  
Contact Resistance: 20mΩ Max.  
Insulation Resistance: 500MΩ Min.  
Withstanding Voltage: 500V AC/minute  
Material: Nylon 66,UL94V-0  
Color: Natural(White)

Circuit No.	Dimensions			
	A	B	C	D
02P	1.25	4.40	2.75	1.10
03P	2.50	5.65	4.00	1.95
04P	3.75	6.90	5.25	3.20
05P	5.00	8.15	6.50	3.20
06P	6.25	9.40	7.75	3.20
07P	7.50	10.65	9.00	3.20
08P	8.75	11.90	10.25	3.20
09P	10.00	13.15	11.50	3.20
10P	11.25	14.40	12.75	3.20
11P	12.50	15.65	14.00	4.70
12P	13.75	16.90	15.25	4.70
13P	15.00	18.15	16.50	4.70
14P	16.25	19.40	17.75	4.70
15P	17.50	20.65	19.00	4.70
16P	18.75	21.90	20.25	4.70
20P	23.75	26.90	25.25	4.70
25P	30.00	33.15	31.50	5.70
30P	36.25	39.40	37.75	5.70





D±0.10  
11P~30P



0.80±0.15  
0.43±0.15

0.60±0.15  
3.00±0.15



±0.05


C±0.15

0.50±0.05  
0.90±0.05  
0.75±0.10

0.90±0.15  
0.89±0.08

SEC:A-A

1.50±0.10  
0.15±0.10



12 HR

5.80±0.25  
1.50±0.10  
2.00±0.15  
3.35±0.20

Circuit 1

B±0.25

						燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.	
						UNIT	SCALE
				mm		1 of 1	1.25mm PITCH HOUSING-LOCK TYPE
				DRAWN BY	APPROVED BY		
				歐陽小強	謝瑞清		
				2007.12.23	2007.12.23		
				GENERAL TOLERANCE			
B0	XXXXXXXXXX	2017.07.05	周傑亮	X.X±0.25	ANGLE±		DRAW NO.: A1253HA-XP
A5	EN1103220076	2011.03.22	陳敏	X.XX±0.15			
REV.	DESCRIPTION	DATE	DATE	X.XXX±0.05			

REV. B0