



Data Sheet

HD-EMB1205-3-SC-R


#### **Features:**

- Designed to be driven with 3 VDC
- Spring Contacts for easy implementation
- Generates 9,000 RPMs with no more than 50 dBA acoustic noise

**Specifications** 

| Parameters                       | Values     | Units    |  |
|----------------------------------|------------|----------|--|
| Rated Voltage                    | 3.0        | VDC      |  |
| Starting Voltage                 | 2.4        | VDC      |  |
| Operating Voltage Range          | 2.5 ~ 3.7  | VDC      |  |
| Direction of Rotation            | CW/CCW     | -        |  |
| Terminal Resistance              | 30 ± 10%   | Ohms     |  |
| Rated Speed (at 3 VDC)           | 9,000      | RPMs     |  |
| Rated Current (at 3 VDC)         | 90         | mA<br>mA |  |
| Starting Current (Max)           | 150        |          |  |
| Shaft Pull Strength              | 3          | Kg       |  |
| Shaft End Play (Max)             | 0.3        | mm       |  |
| Mechanical Noise (Max)           | 50         | dBA      |  |
| Housing Material                 | SPC        | -        |  |
| <b>Environmental Compliances</b> | RoHS/REACH | -        |  |
| Weight                           | 0.8        | Grams    |  |
| Storage Temperature              | -40 ~ +85  | °C       |  |
| Operating Temperature            | -20 ~ +60  | °C       |  |

### **Measurement Methods**




**Reliability Testing** 

| Type of Test              | Test Specifications  |
|---------------------------|--|
|                           | Temperature: 85°C  |
| High Temperature Test     | Test Duration Time: 96 hours   |
|                           | Temperature: -40°C   |
| Low Temperature Test      | Test Duration Time: 96 hours   |
|                           | Temperature: 70°C  |
|                           | Room Humidity: 90%   |
| Humidity Test             | Test Duration Time: 96 hours   |
|                           | Run for two cycles with the motor driving for 0.5 seconds on 0.5 seconds off:  |
| Temperature Cycle Testing | 1 cycle  +60℃  Temperature  -20℃  0 1hr 2hr 3hr  |
| Vibration Test            | 3mm deflection at 1000 cycles per minute, for 10 minutes in each axis (X, Y, Z).   |
| Drop Test                 | Weight: Set linear vibration motor to ~100g (including linear vibration motor) weight of block.  Drop Height: 150cm Floor Material: Steel Test Axis: ±X, ±Y, ±Z; total 6 faces Test Repetition: 2 time per face (12 total) |
| Load Test                 | 1,000,000 operating cycles at room temperature Test Cycle: 0.5 seconds on, 0.5 second off  |

Acceleration, resistance, rated current and noise must meet specifications after allowing the device to rest for 12 hours after test.

©2021, PUI Audio Inc.

## **Dimensions**



# **Packaging**

| ltem      | Tray                    | Inner Box                | Outer Box                |  |
|-----------|-------------------------|--------------------------|--------------------------|--|
| DIV.      | PET                     | Carton box               | Carton box               |  |
| Dimension | 141(L) x 150(W) x 11(H) | 150(L) × 160(W) × 115(H) | 330(L) × 330(W) × 270(H) |  |
| Quantity  | 50ea                    | 1,000ea                  | 8,000ea                  |  |

**Specifications Revisions** 

| Re | vision | Description               | Date       |
|----|--------|---------------------------|------------|
|    | A      | RELEASED FROM ENGINEERING | 04/14/2022 |

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- 2. Specifications subject to change or withdrawal without notice.