

Data Sheet HD-EM1204-LW20-R

PUI Audio's 12.4mm long by 3.8mm wide and high **HD-EM1204-LW20-R** is an eccentric rotating mass vibration haptic motor. Originally designed for use in pagers/beepers, this device is great for use in wearables for haptic feedback.


Features:

- Driven with positive or negative DC for clockwise or counterclockwise movement
- Convenient 20mm lead wires for simple electrical connection
- 13,000 RPMs with 3 VDC input

Specifications

| Parameters | Values | Units |
|------------------------------|---------------|-------|
| Rated Voltage | 3 | VDC |
| Operating Voltage Range | 2.4 ~ 3.6 | VDC |
| Terminal Resistance | 30 ±20% | Ohms |
| Rated Speed (at 3 VDC) | 13,000 ±3,000 | RPMs |
| Current Draw (at 3 VDC) | 90 | mA |
| Stall Current Draw | 120 | mA |
| Insulation Resistance | 1 | MOhms |
| Acoustic Noise (Max) | 45 | dBA |
| Housing Material | SPC | - |
| Acceptable Soldering Methods | Hand Solder | - |
| Environmental Compliances | RoHS/REACH | - |
| Weight | 1 | Grams |
| Storage Temperature | -40 ~ +80 | °C |
| Operating Temperature | -30 ∼ +70 | °C |

Measurement Methods




Specification of the dummy Jig
 Size: 45mm x 105mm x 15mm

Weight: 100grMaterial: Bakelite

· Vibration motor should be attached by using a double-sided tape

Acoustic noise




Reliability Testing

| Type of Test | Test Specifications |
|-------------------------------|---|
| High Temperature Test | 96 hours at 80°C |
| Low Temperature Test | 96 hours at -40°C |
| H2S Corrosion Resistance Test | Concentration: 3 ±1 PPM Test Environment: 40°C, humidity 80% RH Test Duration Time: 240 hours |
| | Temperature: -40°C to +80°C |
| | Test Duration: 30 minutes |
| Temperature Cycle Testing | Test Cycles: 15 cycles |
| Vibration Test | 3mm deflection at 1000 cycles per minute, for 10 minutes in each axis (X, Y, Z). |
| | Weight: Set the linear vibration motor to the around 100g (include the linear vibration motor) weight of block. |
| | Drop Height: 150cm |
| | Floor Material: Steel |
| | Direction: ±X, ±Y, ±Z; total 6 faces |
| Drop Test | Number of Times: Each face 3 Times |
| | 200,000 operating cycles in room temperature |
| Load Test | Cycle test condition: 2 seconds on, 1 second off |

Acceleration, resistance, rated current and noise must meet specifications after allowing the device to rest for 4 hours after test.

Dimensions



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2021, PUI Audio Inc.

Specifications Revisions

| Revision | Description | Date |
|----------|---------------------------|----------|
| A | Released from Engineering | 4/6/2021 |

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- ${\bf 2.} \quad {\bf Specifications \ subject \ to \ change \ or \ with drawal \ without \ notice.}$