

ROX5SJ47K ✓ ACTIVE

Neohm | Neohm ROX

TE Internal #: 1625893-5

47K Ω , Metal Oxide Film, Power Resistor, 5 %, 25 x 8 mm, 2 Termination, Box, 5 W, ± 350 ppm/ $^{\circ}\text{C}$, Copper Termination, Axial-Leaded, Neohm ROX

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Passive Component Dimensions: **25 x 8 mm**

Number of Terminations: **2**

Packaging Method: **Box**

Passive Component Tolerance: **5 %**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Passive Component Tolerance	5 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	47K Ω
Power Rating	5 W

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Number of Terminations	2
Termination Area Base Material	Copper

Dimensions

Passive Component Dimensions	25 x 8 mm
------------------------------	-----------



Usage Conditions

Operating Temperature Range	-55 – 235 $^{\circ}\text{C}$
Temperature Coefficient	± 350 ppm/ $^{\circ}\text{C}$

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance





















For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 3-1625892-1 3W SM M/OX 5% 220R</p>	 <p>TE Part # 1625890-6 2W SM M/OX 5% 10R</p>	 <p>TE Part # 1-1625885-4 1W SM M/OX 5% 10R</p>	 <p>TE Part # 4-1625885-6 1W SM M/OX 5% 22K</p>
 <p>TE Part # 4-1625892-9 3W SM M/OX 5% 3R3</p>	 <p>TE Part # 4-1625892-2 3W SM M/OX 5% 33K</p>	 <p>TE Part # 6-1625892-7 3W SM M/OX 5% 68R</p>	 <p>TE Part # 1-1625892-5 3W SM M/OX 5% 150R</p>
 <p>TE Part # 7-1625890-1 2W SM M/OX 5% 82R</p>	 <p>TE Part # 7-1625890-5 2W SM M/OX 5% 1R5</p>	 <p>TE Part # 2-1625892-1 3W SM M/OX 5% 1K0</p>	 <p>TE Part # 9-1625892-4 ROX3S 5% R22 BL</p>
 <p>TE Part # 1-1625885-2 1W SM M/OX 5% 100R</p>	 <p>TE Part # 4-1625885-4 1W SM M/OX 5% 220R</p>	 <p>TE Part # 7-1625892-2 3W SM M/OX 5% 82K</p>	 <p>TE Part # 1625881-5 1W STD M/OX 2% 47R</p>
 <p>TE Part # 3-1625890-1 2W SM M/OX 5% 220R</p>	 <p>TE Part # 2-1625890-3 2W SM M/OX 5% 1K5</p>	 <p>TE Part # 4-1625892-1 3W SM M/OX 5% 330R</p>	 <p>TE Part # 1-1625885-1 1W SM M/OX 5% 100K</p>

Also in the Series | **Neohm ROX**




Through-Hole Resistors(798)


Customers Also Bought



TE Part #3-1879021-5
SMW3 2R7 5%




TE Part #1217566-1
250 FASTON,PCB TAB,TCBR




TE Part #1-2176083-1
EP 5W (S) 470R 5%




TE Part #1-1625893-0
5W SM M/OX 5% 51K



TE Part #9-2176412-6
5W XSM M/OX 5% 47K



TE Part #1623783-4
SQM7 1K0 5% (METAL FILM)



TE Part #1-2176421-8
TLRP 2512 2.0W R020 1% 25PPM 4K RL



TE Part #384265-E
STVB/2 32 M AB VV 4-00 0606 * * 247 E007

Documents

Product Drawings

5W SM M/OX 5% 47K

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1625893-5_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1625893-5_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1625893-5_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English