

Compact Ferrous Metal Sensor - Non powered Part Number: SRA-SP-006 Top sensing face


Product Data Sheet




PICTURE ✓ RoHS Compliant

SENSING FACE

Sensing face Approximate sensing ranges 75x25x1.5mm Ground flat steel 12x20x30mm Cast iron bar 0.5x20x70mm Tool steel 10x25x50mm Chrome vanadium D6x50mm N35 Neodymium magnet



DIMENSIONS



SPECIFICATION				
Contact Form / Style		Normally Open, closes in presence of ferrous metal		
Activation distance r	mm	6 (may vary depending on iron content)		
Switching Voltage	Max Volts AC/DC	140 / 200		
Switching Current	Max Amps	0.5		
Switching Power M	Max Watts	10		
Carry Current	Max Amps	2.75		
Breakdown Voltage	Min Volts DC	225		
Contact Resistance	Max mOhms	100		
Operating Frequency	Max Hz	100		
Operating Temperature (Celsius	- 40° to 85°		
Case Material		ABS Plastic		
Cable		2 x 20 AWG 105°C Black		

6-9mm

9-10mm

7-10mm

9-10mm

Applications Include

Did you know we also sell?

- Gate closed detection.
- · Robotics sensing.

Image indicative of range

- Automated production lines.
- Safety guards.

- Top or side sensing directions
- Base sensing option (non pin type)
- Custom cable types, cable lengths, connectors or crimp terminals available.

Options

• If you do not see what you need, just ask, as there is a strong possibility we can do it!

Rev. No.	Revision Note	Date	Signature	
1	Datasheet	17-12-15	ML	



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

