





SMK FEMALE COAXIAL TERMINATION 40GHZ 1W

PAGE 1/2 ISSUE 24-02-15B SERIES CHARGE PART NUMBER R404285150







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD OVER NICKEL
Outer contact Insulator	- ULTEM	-
Gasket Substrate	SILICONE RUBBER ALUMINA	
Resistor Others parts	THIN FILM -	-





SMK FEMALE COAXIAL TERMINATION 40GHZ 1W

PAGE <b>2/2</b>	ISSUE <b>24-02-15B</b>	SERIES CHARGE	PART NUMBER <b>R404285150</b>
-----------------	------------------------	------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency (GHz) DC - 40 V.S.W.R  $(\leq)$  1.22

Operating Frequency Range	DC - 40	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	50	W
Average power at 25°C	1	W (Free Air Cooled)
		W (Conduction Cooled)


### **MECHANICAL CHARACTERISTICS**

Connectors	SMA2.9	Male	MIL C 39012
Weight	<b>4,9300</b> g		

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

### Power derating Versus temperature



### **SPECIFICATION**

## **OTHER CHARACTERISTICS**