


DO NOT SCALE
DIMENSIONS IN mm

METRIC



NOTES:

- ① FOR STRIP VERSION SEE DWG. 166046.
- ② UNDERCOATING: 1,3μm Ni.
SELECTIVE : 0,8μm Au.
ZONE I : BRIGHT TIN/LEAD PLATED.
- ③ UNDERCOATING: 1,3μm Ni.
SELECTIVE : 2,0μm Au.
REMAINDER : GOLD FLASH.

WIRE RANGE :
(0,2-0,56 mm²) 20-24 AWG
INSULATION RANGE :
1,57 DIA. MAX.

-	-	-	-	-	-	SEE NOTE ③	BRASS	166296-2
STAINLESS STEEL	SEE NOTE ②	-	-	-	-	SEE NOTE ②	BRASS	166296-1
MATERIAL OF SLEEVE	PLATING OF BODY			MATERIAL OF BODY	PARTNUMBER			
-	-	-	-	-	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED			
-	-	-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.			
-	-	-	-	-	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION , 19-			
-	-	-	-	-	AMP		AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.	
-	-	-	-	-	NAME			
-	-	-	-	-	CONTACT ASSEMBLY-PIN TYPE XI, SIZE 20 LOOSE PIECE			
A	EH-0077-92	JvL	CvT	04-03-94	LTR. REVISION RECORD DR. CHK. DATE			
DR. : J.v.LIEMPT	CHK. : C.v.TILBURG	APP. : J.v.SOEST	DWG. No. C-166296		REV. LTR.	SHEET		
DATE: 6 JAN 1993	DATE: 08-02-93	DATE: 08-02-93			A	1 OF 1		
						A3		