





Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



N=Number of contacts



P.C.B. LAYOUT

Technical Data:
 Electrical
 Pitch: 3.5mm
 Voltage rating: 300V
 Current rating: 12 Amps
 Withstanding Voltage: 2500VAC(1min)
 Mechanical:
 Operating temperature: -40°C to +105°C
 Soldering temperature:
 Temperature= 250°C±10°C /5 seconds max
 Safety approval:
 RoHS Compliance

Part No.:

OSTOQXX1551

No. of Poles
 02 2 Poles
 03 3 Poles

 24 24 Poles

COLOR
 0: Black
 2: Red
 3: Orange
 4: Yellow
 5: Green (Standard)
 6: Blue
 8: Grey

Nonstandard colors
 Mins could apply

3	Flange nut	Copper Alloy						2
2	Pin	Copper Alloy					Tin plated	1xN
1	Body	PA66-30%GF UL94V						1
ITEM	NAME OF PART	MATERIAL	NOTES				Q'TY	
DWG.	DATE	UNITS:	MM	SHEET:	1 OF 1	Tolerance		
CHK.	DATE	SCALE:	NONE 4:1 (:)	REV.: A		X.	±0.50	
APP.	DATE	TITLE:	OSTOQ SERIES 3.5MM			X.XX	±0.30	
			WITH FLANGE RIGHT ANGLE			X°	±1°	
		PART NO.	OSTOQXX1551					
		DWG NO.	OSTOQXX1551.DWG					

REV	△	DESCRIPTION	CHK.	DATE



ON-SHORE TECHNOLOGY, INC.