


Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	△	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICATION STANDARD											
RATING	OPERATING TEMPERATURE RANGE		-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE		-10 °C TO 60 °C			
	VOLTAGE		AC 50 V			OPERATING HUMIDITY RANGE		RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED)			
	CURRENT		0.3 A								
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENT				QT	AT
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING				X	X
MARKING		CONFIRMED VISUALLY.								X	X
ELECTRICAL CHARACTERISTICS											
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).				70 mΩ MAX.				X	X
INSULATION RESISTANCE		100 V DC.				100 MΩ MIN.				X	—
VOLTAGE PROOF		150 V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN.				X	X
MECHANICAL CHARACTERISTICS											
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.				INSERTION FORCE: 48 N MAX. WITHDRAWAL FORCE: 2 N MIN.				X	—
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.				1) CONTACT RESISTANCE: 80 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	—
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm, — m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.				1) NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.								X	—
ENVIRONMENTAL CHARACTERISTICS											
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.				1) CONTACT RESISTANCE: 80 mΩ MAX. 2) INSULATION RESISTANCE: 100 MΩ MIN.				X	—
RAPID CHAGE OF TEMPERTURE		TEMPERTURE -55→-15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3 min. UNDER 5 CYCLES.				3) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	—
DRY HEAT COLD		EXPOSED AT 85 °C, 96 h. EXPOSED AT -55 °C, 96 h.				1) CONTACT RESISTANCE: 80 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.				NO HEAVY CORROSION.				X	—
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)				1) CONTACT RESISTANCE: 80 mΩ MAX. 2) NO HEAVY CORROSION.				X	—
RESISTANCE TO SOLDERING HEAT		REFLOW : RECOMMENDED TEMPERATURE PROFILE  TO BE TESTED UNDER THE ABOVE CONDITIONS.				NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.				X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s.				NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.				X	—
REMARKS					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED		
					<i>J. Mitsuoka</i> 00.06.20	<i>J. Mitsuoka</i> 00.06.20	<i>H. Okawa</i> 00.06.21	<i>J. Fujimura</i> 00.06.23			
UNLESS OTERWISE SPECIFIED, REFER TO JIS C 5402.											
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST											
HRS HIROSE ELECTRIC CO., LTD.						SPECIFICATION SHEET			PART NO. FX11B - 80P - SV0.5 (21)		
CODE NO.(OLD) CL			DRAWING NO. ELC4 - 152631 - 01			CODE NO. CL 573 - 0658- 9 - 21			1 1		

