PROPRIETARY INFORMATION:		REVISION				
PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.	REV	DESCRIPTION	DATE	APPROVED		
	A	INITIAL RELEASE, RFS.4648, DMR	09/30/04	DMR		
	В	CORRECTION, TYPO MARKING, RFS.5272, DMR	12/28/04	DMR		
	С	UPDATE DRAWING, RFS. 8597,SO	06/09/06	HM		

1. NOTES:

DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE.

2. ELECTRICAL SPECIFICATIONS:

INPUT VOLTAGE: $5 \text{ VDC} \pm 10\%$ INPUT CURRENT: < 0.35 A

OUTPUT VOLTAGE / CURRENT: +5.0 VDC @ 200 mA

OUTPUT CURRENT: NO LOAD TO FULL LOAD, 10% MINIMUM LOAD REQUIRED TO

MAINTAIN SPECIFIED REGULATION

OUTPUT POWER (RATED): 1 WATTS MAX SWITCHING FREQUENCY: 100 MHz TYP.

OUTPUT RIPPLE (PEAK TO PEAK): 20 MHz BAND LIMITED

 \leq 150mV @ Iv = 3.3 VDC AND 48.0VDC \leq 100mV @ Iv = 5.0 VDC AND 24.0VDC

OUTPUT VOLTAGE ACCURACY: $\leq \pm 5\%$

OUTPUT REGULATION (LINE/LOAD): \pm 5 % MEASURED AT O/P PINS

LINE REGULATION: $\pm 1.2\% / 1\%$ OF Vin MAX AT FULL LOAD

LOAD REGULATION: 15% MAX AT FULL LOAD

TURN ON/ TURN OFF OVERSHOOT: 4% MAX 500uS MAX RECOVERY TIME FOR 25% STEP LOAD

TURN-ON DELAY: 1 SEC MAX

EFFICIENCY: 70 %

ISOLATION RESISTANCE: 100 Mohm MIN @ 500 VDC

DIELECTRIC WITHSTAND VOLTAGE: 1000 VDC MIN. PRIMARY TO SECONDARY

OPERATING TEMPERATURE: 0°C TO 70° C STORAGE TEMPERATURE: -20°C TO 80° C

HUMIDITY: 0 TO 95% RELATIVE HUMIDITY

Foot Note: Globtek Inc. will not be liable for the	DASH NO.	PART NO	REV.			DESCRIPTION		NOTES	
safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult for the proper installation	TABULATION BLOCK								
instruction the applicable UL, $\!$			TOL DECIM .xx +/-		G Glo	bTek [°] , Inc.	186 Veterans Dr. North Tel. 201-784-1000 Fax		
Limitation of Use: Globtek product are not authorized for use as			.xxx +/005		ww	w.globtek.com	101. 201-704-1000 Fax	201./64.0111	
mission critical components in life support, hazardous environment, nuclear or aircraft applications without prior written	INIT.BY: DMR	DATE: 09/30/04	MILLIME .xx +/- .xxx +/-	0.3 +/- 1*	DWG TITLE:	DC / DC CONVERT 1W, I/P: 5 VDC; O/P	ER, SINGLE : 5 VDC		
approval from the CEO of Globtek Inc.	DRAWN: NF	DATE: 09/30/04	FSCN : G, Y	No.: SIZE A	MODEL NO:	DB10B1BH1		REV. C	
Contents of this document are subject to change without prior notice	APRVD : DMR	DATE: 09/30/04	SCAL	E: NONE	PART NO:	DB10B1BH1		SHEET 1 OF 2	

PROPRIETARY INFORMATION:


PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.

3. MECHANICAL DIMENSIONS: MM

HOUSING: 7 PIN SIP PACKAGE, 94V- 0 PLASTIC MATERIAL WITH 94V-0 POTTING MATERIAL, BLACK

4. MARKING: PERMANENT PAD PRINTING, WHITE:

I/P: 3.3V - 24V



ITEM	SPECIFICATION	READING	
Α	19.50	19.53	
В	6.00	5.94	
С	10.00	10.05	
D	12.70	12.69	
Е	4.00	4.03	
F	0.50±0.05	0.51	
G	2.00	2.02	
Н	1.25	1.26	
I	0.50±0.05	0.49	
J	0.25±0.05	0.26	
K	2.54	2.54	

PIN	OUTPUT
1	+ INPUT
2	- INPUT
4	- OUTPUT
6	+ OUTPUT

GlobTek, Inc.	186 Veterans Dr. Northval Tel. 201-784-1000 Fax 20				
DWG TITLE: DC / DC CONVERTER, SINGLE 1W, I/P: 5 VDC; O/P: 5 VDC					
MODEL NO: DB10B1BH1		REV. C			
PART NO: DB10B1BH1		SHEET 2 OF 2			