


REV. 0
DCO 17615

COIL: @ 25°C	
RESISTANCE	600 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
MUST RELEASE	8.5 VDC MAX, 2.7 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 2000 Hz @ 30 g's
SHOCK	100 g's 11 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	
OPERATE TIME:	5 MS MAX
RELEASE TIME:	4 MS MAX
CONTACT BOUNCE:	2.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2 AMPS
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 19 JUN 02 | *ASB 6/19/02*

CII Technologies
advanced control electronic solutions

CUST. GENICOM
CUST. NO. 3SAF5062H1 REV. _____

TYPE "FW" RELAY

FW 11133S01