

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD														
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C										
	VOLTAGE	50V AC	APPLICABLE CONNECTOR	DF17# (**)-*DS-0.5V (**)										
	CURRENT	0.3A												
SPECIFICATIONS														
ITEM	TEST METHOD		REQUIREMENTS	QT	AT									
CONSTRUCTION														
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X									
MARKING	CONFIRMED VISUALLY.			X	X									
ELECTRIC CHARACTERISTICS														
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).		60mΩ MAX.	X	-									
INSULATION RESISTANCE	100V DC.		500MΩ MIN.	X	-									
VOLTAGE PROOF	150V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	-									
MECHANICAL CHARACTERISTICS														
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.		<table border="1"> <thead> <tr> <th>SIGNAL</th> <th>INSERTION FORCE (N)MAX</th> <th>WITHDRAWAL FORCE (N)MIN</th> </tr> </thead> <tbody> <tr> <td>26</td> <td>26.0</td> <td>2.6</td> </tr> <tr> <td>80</td> <td>80.0</td> <td>8.0</td> </tr> </tbody> </table>	SIGNAL	INSERTION FORCE (N)MAX	WITHDRAWAL FORCE (N)MIN	26	26.0	2.6	80	80.0	8.0	X	-
SIGNAL	INSERTION FORCE (N)MAX	WITHDRAWAL FORCE (N)MIN												
26	26.0	2.6												
80	80.0	8.0												
MECHANICAL OPERATION	50TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 60mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-									
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-									
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-									
ENVIRONMENTAL CHARACTERISTICS														
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35°C TIME 30→10 TO 15→ 30→10TO15min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-									
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 250 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-									
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	-									
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JEIDA-39)		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	-									
HEAT RESISTANCE OF SOLDERING	[RECOMMENDED TEMPERATURE PROFILE] 《SOLDERING AREA》 MAX250°C, 220°C FOR 60 SECONDS MAX. 《PREHEATING AREA》 150 TO 180°C 120 SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. [RECOMMENDED MANUAL SOLDELING CONDITION] SOLDERING IRON TEMPERATURE 350°C SOLDERING TIME : WITHIN 3 SECONDS.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.											
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE										
△														
REMARKS			APPROVED	MO. NAKAMURA	05.04.05									
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT.			CHECKED	TS. MIYAZAKI	05.04.05									
UNLESS OTHERWISE SPECIFIED,REFER TO JIS C 5402.			DESIGNED	YH. MICHIDA	05.04.05									
			DRAWN	YH. MICHIDA	05.04.05									
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-163274-04											
SPECIFICATION SHEET HIROSE ELECTRIC CO., LTD.		PART NO.	DF17 (2.5)-*DP-0.5V (57)											
		CODE NO.	CL683	△	1/1									