





Jan.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard					
Rating	Operating temperature range	-55°C to + 105°C(Note 1)	Storage temperature range	-10°C to + 60°C(Note 3)	
	Operating humidity range	40% to + 80%(Note 2)	Storage humidity range	40% to + 70%(Note 3)	
	Applicable contact	DF3-22SC * DF3-2428SC *	Applicable cable	UL1007 AWG24 to 28 UL1061 AWG22 to 28	
	Voltage	250V AC/DC	UL·CSA Rating	Voltage	30V AC/DC
	Current	AWG 22 to 24 : 3A/pin AWG 26 : 2A/pin AWG 28 : 1A/pin		Current	AWG 24 : 3A/pin AWG 26 : 2A/pin AWG 28 : 1A/pin 
Specifications					
Item	Test method	Requirements	QT	AT	
Construction					
General examination	Visually and by measuring instrument.	According to drawing.	X	X	
Marking	Confirmed visually.		X	X	
Electric characteristics					
Insulation resistance	500V DC.	1000MΩ MIN.	X	-	
Voltage proof	650V AC for 1 min.	No flashover or breakdown.	X	-	
Mechanical characteristics					
Mechanical operation	50 times insertions and extractions.	1) No damage, crack or looseness of parts.	X	-	
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 2 h, for 3 directions.	1) No damage, crack or looseness of parts.	X	-	
Shock	490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.	1) No damage, crack or looseness of parts.	X	-	
Environmental characteristics					
Rapid change of temperature	Temperature -55→ 5 to 35→ 85→ 5 to 35 °c Time 30→ 5MAX → 30→ 5MAX min Under 5 cycles.	1) Insulation resistance: 1000MΩ MIN. 2) No damage, crack or looseness of parts.	X	-	
Damp heat (Steady state)	Exposed at 40 ± 2 °c, 90 to 95 %, 96 h.	1) Insulation resistance: 500MΩ MIN. 2) No damage, crack or looseness of parts.	X	-	
Remarks					
Note 1:Including the temperature rise by current Note 2:No condensing. Note 3:Apply to an unused product on the packaged condition.					
	Count	Description of revisions	Designed	Checked	Date
	1	DIS-H-00008205	SN. MIWA	SZ. ONO	20210312
Unless otherwise specified , refer to IEC 60512.			Approved	KJ. KATAYOSE	20050105
			Checked	KI. AKIYAMA	20050105
			Designed	TH. ARAI	20050105
			Drawn	TH. ARAI	20050105
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing no.	ELC-162387-00-01	
	Specification sheet		Part no.	DF3-*S-2C	
	Hirose electric co., ltd.		Code no.	CL543-	 1/1