



P-Ch 150V Fast Switching MOSFETs

Description


The HSH25P15 uses advanced trench MOSFET technology to provide excellent $R_{DS(ON)}$ and gate charge for use in a wide variety of other applications.

The HSH25P15 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

Product Summary

V_{DS}	-150	V
$R_{DS(ON),max}$	150	mΩ
I_D	-23	A

TO-263 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-150	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_c=25^\circ C$	Continuous Drain Current, $V_{GS} @ -10V^1$	-23	A
$I_D@T_c=100^\circ C$	Continuous Drain Current, $V_{GS} @ -10V^1$	-15	A
I_{DM}	Pulsed Drain Current ²	-85	A
EAS	Single Pulse Avalanche Energy ³	220	mJ
I_{AS}	Avalanche Current	24	A
$P_D@T_c=25^\circ C$	Total Power Dissipation ⁴	100	W
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	62	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	1.2	°C/W



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$, $I_D=-250\mu\text{A}$	-150	---	---	V
$R_{\text{DS(ON)}}$	Static Drain-Source On-Resistance ²	$V_{\text{GS}}=-10\text{V}$, $I_D=-20\text{A}$	---	130	150	$\text{m}\Omega$
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{GS}}=V_{\text{DS}}$, $I_D=-250\mu\text{A}$	-2.0	-2.8	-4.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{\text{DS}}=-120\text{V}$, $V_{\text{GS}}=0\text{V}$, $T_J=25^\circ\text{C}$	---	---	-1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{\text{GS}}=\pm 20\text{V}$, $V_{\text{DS}}=0\text{V}$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{\text{DS}}=-10\text{V}$, $I_D=-20\text{A}$	---	13	---	S
Q_g	Total Gate Charge	$V_{\text{DS}}=-75\text{V}$, $V_{\text{GS}}=-10\text{V}$, $I_D=-10\text{A}$	---	56	---	nC
Q_{gs}	Gate-Source Charge		---	11	---	
Q_{gd}	Gate-Drain Charge		---	8.5	---	
$T_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}}=-75\text{V}$, $V_{\text{GS}}=-10\text{V}$, $R_G=6\Omega$, $I_D=-10\text{A}$	---	33	---	ns
T_r	Rise Time		---	19	---	
$T_{\text{d(off)}}$	Turn-Off Delay Time		---	149	---	
T_f	Fall Time		---	50	---	
C_{iss}	Input Capacitance	$V_{\text{DS}}=-75\text{V}$, $V_{\text{GS}}=0\text{V}$, $f=1\text{MHz}$	---	3600	---	pF
C_{oss}	Output Capacitance		---	455	---	
C_{rss}	Reverse Transfer Capacitance		---	186	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_s	Continuous Source Current ^{1,5}	$V_G=V_D=0\text{V}$, Force Current	---	---	-23	A
V_{SD}	Diode Forward Voltage ²	$V_{\text{GS}}=0\text{V}$, $I_s=-1\text{A}$, $T_J=25^\circ\text{C}$	---	---	-1.3	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{\text{DD}}=-75\text{V}$, $V_{\text{GS}}=-10\text{V}$, $L=0.5\text{mH}$, $I_{\text{AS}}=-24\text{A}$
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.



Typical Characteristics

Figure 1. Output Characteristics




Figure 3. On-Resistance vs.
Gate-Source Voltage




Figure 5. Gate Threshold Variation
with Temperature




Figure 2. Body Diode Forward Voltage
Variation with Source Current




Figure 4. On-Resistance Variation with
Drain Current and Temperature




Figure 6. Gate Charge






Figure 7. Capacitance




Figure 8. Maximum Safe Operating Area






Figure 9. Normalized Thermal Transient Impedance Curve



SYMBOLS	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.370	4.770	0.172	0.188
A1	1.220	1.420	0.048	0.056
A2	2.200	2.890	0.087	0.114
A3	0.000	0.250	0.000	0.010
b	0.700	0.960	0.028	0.038
b1	1.170	1.470	0.046	0.058
c	0.300	0.530	0.012	0.021
D1	8.500	9.300	0.335	0.366
D4	6.600	-	0.260	-
E	9.860	10.36	0.388	0.408
E5	7.060	-	0.278	-
e	2.540 BSC		0.100 BSC	
H	14.70	15.70	0.579	0.618
H2	1.070	1.470	0.042	0.058
L	2.000	2.600	0.079	0.102
L1	1.400	1.750	0.055	0.069
L4	0.250 BSC		0.010 BSC	
θ	0°	9°	0°	9°