

RN73C1J110KBTD ✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 7-1879140-5

110K Ω , Thin Film, Precision Resistor, .1 %, 2 Termination, 0603, Taped & Reeled, .063 W, ± 10 ppm/ $^{\circ}\text{C}$, Solder, Height .018 in [.45 mm], Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0603**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0603
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Passive Component Tolerance	.1 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	110K Ω
Power Rating	.063 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

Usage Conditions

Temperature Coefficient	± 10 ppm/ $^{\circ}$ C
-------------------------	----------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 <p>TE Part # 7-1879140-6 RN 0603 113K 0.1% 10PPM 5K RL</p>	 <p>TE Part # 7-1879140-4 RN 0603 107K 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-1 RN 0603 18K2 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-2 RN 0603 18K7 0.1% 10PPM 5K RL</p>
 <p>TE Part # 1879140-3 RN 0603 19K1 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-4 RN 0603 19K6 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-5 RN 0603 20K5 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-6 RN 0603 21K 0.1% 10PPM 5K RL</p>
 <p>TE Part # 2-1879137-0 RN 0603 221R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 2-1879137-1 RN 0603 226R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-8 RN 0603 22K1 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1879140-9 RN 0603 22K6 0.1% 10PPM 5K RL</p>
 <p>TE Part # 2-1879137-2 RN 0603 232R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 2-1879137-3 RN 0603 237R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1-1879140-0 RN 0603 23K2 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1-1879140-1 RN 0603 23K7 0.1% 10PPM 5K RL</p>
 <p>TE Part # 2-1879137-4 RN 0603 243R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 2-1879137-5 RN 0603 249R 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1-1879140-2 RN 0603 24K3 0.1% 10PPM 5K RL</p>	 <p>TE Part # 1-1879140-3 RN 0603 24K9 0.1% 10PPM 5K RL</p>

Also in the Series | [Holsworthy RN73](#)



Customers Also Bought



Documents

Product Drawings

[RN 0603 110K 0.1% 10PPM 5K RL](#)

English

Datasheets & Catalog Pages

[High Precision Resistors \(SMD\) - Type RN73 Series - Tyco Electronics Passives](#)

English