

Description

The HSBA4119 is the high cell density trenched P-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.


The HSBA4119 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

- Super Low Gate Charge
- 100% EAS Guaranteed
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

Product Summary

V _{DS}	-40	V
R _{DS(ON),typ}	3.1	mΩ
I _D	-120	A

PRPAK5X6 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	-40	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current, V _{GS} @ -10V ^{1,6}	-120	A
I _D @T _C =100°C	Continuous Drain Current, V _{GS} @ -10V ^{1,6}	-90	A
I _{DM}	Pulsed Drain Current ²	-580	A
EAS	Single Pulse Avalanche Energy ³	1250	mJ
I _{AS}	Avalanche Current	-70	A
P _D @T _C =25°C	Total Power Dissipation ⁴	150	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient ¹ (t ≤ 10S)	---	20	°C/W
	Thermal Resistance Junction-ambient ¹ (Steady State)	---	62	°C/W
R _{θJC}	Thermal Resistance Junction-case ¹	---	1.5	°C/W

Electrical Characteristics ($T_J=25\text{ }^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-40	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=-10V, I_D=-30A$	---	3.1	3.8	$m\Omega$
		$V_{GS}=-4.5V, I_D=-20A$	---	4.0	5.6	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=-250\mu A$	-1.0	---	-2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-40V, V_{GS}=0V, T_J=25^\circ C$	---	---	-1	μA
		$V_{DS}=-40V, V_{GS}=0V, T_J=125^\circ C$	---	---	-100	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
R_g	Gate resistance	$V_{DS}=0V, V_{GS}=0V, f=1MHz$		1.7		Ω
Q_g	Total Gate Charge (-10V)	$V_{DS}=-20V, V_{GS}=-10V, I_D=-20A$	---	190	---	nC
Q_{gs}	Gate-Source Charge		---	24	---	
Q_{gd}	Gate-Drain Charge		---	38	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=-20V, V_{GS}=-10V, R_G=3\Omega, I_D=-10A$	---	18	---	ns
T_r	Rise Time		---	3.6	---	
$T_{d(off)}$	Turn-Off Delay Time		---	21	---	
T_f	Fall Time		---	39	---	
C_{iss}	Input Capacitance	$V_{DS}=-20V, V_{GS}=0V, f=1MHz$	---	10700	---	pF
C_{oss}	Output Capacitance		---	780	---	
C_{rss}	Reverse Transfer Capacitance		---	660	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current	---	---	-120	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V, I_S=-20A, T_J=25^\circ C$	---	---	-1.2	V
t_{rr}	Reverse Recovery Time	$I_F=-20A, di/dt=100A/\mu s,$	---	52	---	nS
Q_{rr}	Reverse Recovery Charge	$T_J=25^\circ C$	---	128	---	nC

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{DD}=-40V, V_{GS}=-10V, L=0.5mH, I_{AS}=-70A$
- 4.The power dissipation is limited by 150 $^\circ C$ junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation
- 6.The maximum current rating is package limited.



Typical Characteristics




Fig.1 Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 Power Dissipation




Fig.4 Drain Current




Fig.5 BV_{dss} vs Junction Temperature




Fig.6 $R_{ds(on)}$ vs Junction Temperature




Fig.7 Gate Charge Waveforms




Fig.8 Capacitance




Fig.9 Body-Diode Characteristics






Fig.10 Maximum Safe Operating Area

Ordering Information

Part Number	Package code	Packaging
HSBA4119	PRPAK5*6	3000/Tape&Reel



SYMBOLS	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.80	--	1.20	0.031	--	0.047
B	0.30	--	0.51	0.012	--	0.020
C	0.15	--	0.35	0.006	--	0.014
D	4.80	--	5.30	0.189	--	0.209
D2	3.61	--	4.35	0.142	--	0.171
E	5.90	--	6.35	0.232	--	0.250
E2	5.42	--	5.90	0.213	--	0.232
E3	3.23	--	3.90	0.127	--	0.154
E4	3.69	--	4.55	0.145	--	0.179
L	0.61	--	1.80	0.024	--	0.071
L2	0.05	--	0.36	0.002	--	0.014
e	--	1.27	--	--	0.050	--